Product data sheet

Specifications





TeSys SK control relay - 2 NO - <= 690 V - 380 V AC coil

CA2SKE20Q7

() Discontinued on: Dec 30, 2023

① Discontinued

Main

Range	TeSys	
Product Name	TeSys CASK	
Product Or Component Type	Control relay	
Device Short Name	CA2SKE	
Contactor Application	Control circuit	
Utilisation Category	DC-13 AC-15	
Pole Contact Composition	2 NO	
[Ue] Rated Operational Voltage	<= 690 V <= 400 Hz	
Control Circuit Type	AC 50/60 Hz	
[Uc] Control Circuit Voltage	380 V AC 50/60 Hz	

Complementary

10 A (at 131 °F (55 °C))
10 A gL conforming to VDE 0660 10 A gL conforming to IEC 60947
690 V IEC 60947 690 V VDE 0110 group C 690 V BS 5424 690 V UL 508 690 V CSA C22.2 No 14
Plate Rail
screw clamp terminals 1 0.000.01 in ² (1.56 mm ²)solid screw clamp terminals 2 0.000.01 in ² (1.54 mm ²)solid screw clamp terminals 1 0.000.01 in ² (0.56 mm ²)flexible without cable end screw clamp terminals 1 0.000.01 in ² (0.356 mm ²)flexible with cable end screw clamp terminals 2 0.000.00 in ² (0.351.5 mm ²)flexible with cable end screw clamp terminals 2 0.000.00 in ² (0.352.5 mm ²)flexible without cable end
7.08 lbf.in (0.8 N.m) screw clamp terminals pozidriv No 1
Drop-out: 0.20.75 Uc (at <122 °F (50 °C)) Operational: 0.851.1 Uc (at <122 °F (50 °C))
68 ms coil de-energisation and NO opening 714 ms coil energisation and NO closing
10 Mcycles
1200 cyc/h
23 VA (at 68 °F (20 °C))

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Hold-In Power Consumption In Va	4.9 VA (at 68 °F (20 °C))
Heat Dissipation	1.5 W
Height	2.28 in (58 mm)
Width	1.77 in (45 mm)
Depth	2.68 in (68 mm)
Net Weight	0.29 lb(US) (0.132 kg)

Environment

Standards	EN/IEC 60947-5-1 UL 60947-5-1 CSA C22.2 No 60947-5-1	
Product Certifications	CB Scheme cULus EAC CE UKCA	
Ip Degree Of Protection	IP2X	
Protective Treatment	TC IEC 60068	
Ambient Air Temperature For Operation	-4122 °F (-2050 °C)	
Ambient Air Temperature For Storage	-58158 °F (-5070 °C)	
Operating Altitude	6561.68 ft (2000 m) without derating	

Ordering and shipping details

Category	22371-RELAYS, CONTROL	
Discount Schedule	112	
Gtin	3389110567137	
Returnability	No	
Country Of Origin	CZ	

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.93 in (4.900 cm)
Package 1 Width	2.36 in (6.000 cm)
Package 1 Length	2.95 in (7.500 cm)
Package 1 Weight	6.31 oz (179.000 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	24
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	5.91 in (15.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	9.97 lb(US) (4.521 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information