

Product data sheet

Specifications



Fuse carrier, TeSys DF, 1P+N, 125A, 690VAC, fuse size 22x58mm, blown fuse indicator

DF221NV

⚠ Discontinued on: May 5, 2023

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	TeSys
Product Name	TeSys DF
Product Or Component Type	Fuse carrier
Device Short Name	DF22
Device Composition	tubular link locked in Neutral pole
Product Compatibility	DF2FA fuse cartridge DF2FN fuse cartridge
Poles Description	1P + N
Fuse Size	22 x 58 mm
Fuse Type	, aM , gG
Control Type	Toggle
Local Signalling	Blown fuse indication
[Ue] Rated Operational Voltage	690 V AC 690 V DC
[Ie] Rated Operational Current	125 A
[Ui] Rated Insulation Voltage	690 V AC
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ipk] Rated Peak Withstand Current	19 kA with tubular links IEC 60269-1
Short-Circuit Withstand	120 kA 400 V IEC 60947-3 120 kA 500 V IEC 60947-3 80 kA 690 V IEC 60947-3

Complementary

Standards	EN/IEC 60947-3 EN/IEC 60269-2 UL 4248-1 CSA C22.2 No 4248-1
Product Certifications	IEC UL Recognized CSA EAC
Mounting Support	35 mm symmetrical DIN rail
Mounting Position	Vertical +/- 23°)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Connections - Terminals	screw clamp terminals 1 0.00...0.05 in² (2.5...35 mm²)rigid screw clamp terminals 2 0.00...0.04 in² (2.5...25 mm²)rigid screw clamp terminals 1 0.00...0.05 in² (2.5...35 mm²)flexible with or without screw clamp terminals 2 0.00...0.04 in² (2.5...25 mm²)flexible with or without
Tightening Torque	35.40 lbf.in (4 N.m)
Height	5.02 in (127.5 mm)
Width	2.76 in (70 mm)
Depth	3.01 in (76.5 mm)
Net Weight	1.01 lb(US) (0.459 kg)
Quantity Per Set	Set of 3

Environment

Ambient Air Temperature For Storage	-40...176 °F (-40...80 °C)
Ambient Air Temperature For Operation	-4...140 °F (-20...60 °C) with derating above 20°C
Ip Degree Of Protection	IP20 conforming to IEC 60529
Protective Treatment	TH
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1
Compatibility Code	DF22

Ordering and shipping details

Category	US10CP121714
Discount Schedule	0CP1
Gtin	3389118233416
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7 cm)
Package 1 Width	3.03 in (7.7 cm)
Package 1 Length	5.04 in (12.8 cm)
Package 1 Weight	12.70 oz (360 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	3
Package 2 Height	3.35 in (8.5 cm)
Package 2 Width	5.16 in (13.1 cm)
Package 2 Length	8.86 in (22.5 cm)
Package 2 Weight	2.70 lb(US) (1.226 kg)
Unit Type Of Package 3	S03
Number Of Units In Package 3	27
Package 3 Height	11.81 in (30 cm)
Package 3 Width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

Package 3 Weight	23.00 lb(US) (10.433 kg)
------------------	--------------------------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65		WARNING: Cancer - www.P65Warnings.ca.gov