




Price\* : 35.50 USD



ⓘ Discontinued

CA2KN407M7 has not been replaced. Please contact your customer care center for more information.

## Main

Range	TeSys
Product name	TeSys CAK
Product or component type	Control relay
Device short name	CA2K
Contactor application	Control circuit
Utilisation category	AC-15 DC-13
Pole contact composition	4 NO
System Voltage	$\leq 690$ V $\leq 400$ Hz
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	220...230 V AC 50/60 Hz

## Complementary

[Ith] conventional free air thermal current	10 A at $\leq 122$ °F (50 °C)
Irms rated making capacity	110 A conforming to IEC 60947
Associated fuse rating	10 A gG conforming to IEC 60947 10 A gG conforming to VDE 0660
[Ui] rated insulation voltage	600 V conforming to CSA C22.2 No 14 690 V conforming to BS 5424 690 V conforming to IEC 60947 750 V conforming to VDE 0110 group C
Mounting support	Plate Rail
Connections - terminals	Faston terminals 1 6.35 mm Faston terminals 2 2.8 mm
Control circuit voltage limits	0.8...1.15 Uc at 122 °F (50 °C) operational 0.2...0.75 Uc at 122 °F (50 °C) drop-out
Operating time	10...20 ms coil de-energisation and NO opening 10...20 ms coil energisation and NO closing

Mechanical durability	10 Mcycles
Operating rate	10000 cyc/h
Immunity to microbreaks	2 ms
Inrush power in VA	30 VA at 68 °F (20 °C)
Hold-in power consumption in VA	4.5 VA at 68 °F (20 °C)
Heat dissipation	1.3 W
Minimum switching voltage	17 V
Minimum switching current	5 mA
Non overlap distance	0.02 in (0.5 mm)
Insulation resistance	> 10 MOhm
Height	2.28 in (58 mm)
Width	1.77 in (45 mm)
Depth	2.24 in (57 mm)
Product weight	0.4 lb(US) (0.18 kg)


## Environment

Standards	BS 5424 IEC 60947 VDE 0660 NF C 63-140
Product certifications	CSA UL
Protective treatment	TC conforming to IEC 60068
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-58...176 °F (-50...80 °C)
Operating altitude	6561.68 ft (2000 m) without derating
Flame retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102
Mechanical robustness	Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6 Vibrations contactor open 2 Gn, 5...300 Hz IEC 60068-2-6 Shocks contactor open 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed 15 Gn for 11 ms IEC 60068-2-27

## Ordering and shipping details

Category	22371 - RELAYS, CONTROL
Discount Schedule	I12
Nbr. of units in pkg.	1
Package weight(Lbs)	0.4199999999999998
Returnability	N

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant  <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---