


GS1AF43 has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

## Main

Range of product	TeSys
Device short name	GS1AF
Product or component type	Auxiliary contact
Contact application	Blown fuse signalling
Contacts type and composition	1 C/O
Contact operation	Instantaneous
[I <sub>th</sub> ] conventional free air thermal current	16 A at 104 °F (40 °C)
[I <sub>e</sub> ] rated operational current	12 A at 24 V DC-13 2 A at 48 V DC-13 3 A at 400 V AC-15 4 A at 230 V AC-15 0.4 A at 220 V DC-13 0.6 A at 110 V DC-13

## Complementary

Range compatibility	TeSys , TeSys GS ,fuse-switch disconnecter
Mechanical durability	30000 cycles
Electrical durability	30000 cycles on AC-15
Product compatibility	GS
Poles description	3P
Line Rated Current	400 A 250 A
Fuse type	NFC DIN
Fuse size	2 1
Product weight	0.08 lb(US) (0.038 kg)

## Ordering and shipping details

Category	18402 - WORLD SERVICE PARTS(CONTROL ACCESS)
Discount Schedule	CP10
Nbr. of units in pkg.	1
Package weight(Lbs)	8.0000000000000002E-2

Returnability	N
---------------	---

**Offer Sustainability**

RoHS (date code: YYWW)	Compliant - since 0724 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------