# **Product data sheet**

Specifications

Main





! Discontinued

# Control relay, TeSys K, 4 NO, It or eq to 690V, 120VAC coil

CA2KN40G72

Discontinued on: Jul 12, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

man i		
Range	TeSys	
Product Name	TeSys CAK	
Product Or Component Type	Control relay	
Device Short Name	CA2K	
Contactor Application	Control circuit	
Utilisation Category	DC-13 AC-15	
Pole Contact Composition	4 NO	
[Ue] Rated Operational Voltage	e <= 690 V <= 400 Hz	
Control Circuit Type	AC 50/60 Hz	
[Uc] Control Circuit Voltage	120 V AC 50/60 Hz	

#### Complementary

o o in promontary		
Coil Technology	nnology Built-in bidirectional peak limiting diode suppressor	
[Ith] Conventional Free Air Thermal Current	10 A (at 122 °F (50 °C))	
Irms Rated Making Capacity	110 A IEC 60947	
Associated Fuse Rating	10 A gG conforming to IEC 60947 10 A gG conforming to VDE 0660	
[Ui] Rated Insulation Voltage	690 V IEC 60947 750 V VDE 0110 group C 690 V BS 5424 600 V CSA C22.2 No 14	
Mounting Support	Plate Rail	
Connections - Terminals	screw clamp terminals 1 0.000.01 in² (1.54 mm²)solid screw clamp terminals 2 0.000.01 in² (1.54 mm²)solid screw clamp terminals 1 0.000.01 in² (0.754 mm²)flexible with cable end screw clamp terminals 2 0.000.01 in² (0.754 mm²)flexible without cable end screw clamp terminals 1 0.000.00 in² (0.341.5 mm²)flexible with cable end screw clamp terminals 2 0.000.00 in² (0.341.5 mm²)flexible without cable end	
Tightening Torque	11.51 lbf.in (1.3 N.m) screw clamp terminals flat Ø 6 mm 11.51 lbf.in (1.3 N.m) screw clamp terminals Philips No 2 0.24 in (6 mm)	
Control Circuit Voltage Limits	rol Circuit Voltage Limits Drop-out: 0.20.75 Uc (at <122 °F (50 °C)) Operational: 0.81.15 Uc (at <122 °F (50 °C))	
Operating Time	1020 ms coil de-energisation and NO opening 1020 ms coil energisation and NO closing	
Mechanical Durability	10 Mcycles	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Maximum Operating Rate	10000 cyc/h
Immunity To Microbreaks	2 ms
Inrush Power In Va	30 VA (at 68 °F (20 °C))
Hold-In Power Consumption In Va	4.5 VA (at 68 °F (20 °C))
Heat Dissipation	1.3 W
Minimum Switching Voltage	17 V
Minimum Switching Current	5 mA
Non Overlap Distance	0.02 in (0.5 mm)
Insulation Resistance	> 10 MOhm
Height	2.28 in (58 mm)
Width	1.77 in (45 mm)
Depth	2.24 in (57 mm)
Net Weight	0.40 lb(US) (0.18 kg)

#### **Environment**

Standards	EN/IEC 60947-4-1	
	GB/T 14048.4	
	UL 60947-4-1	
	CSA C22.2 No 60947-4-1	
	JIS C8201-4-1	
Product Certifications	CB Scheme	
	CCC	
	UL	
	CSA	
	EAC	
	CE	
	UKCA	
Ip Degree Of Protection	IP2X	
Protective Treatment	TC IEC 60068	
Ambient Air Temperature For Operation	-13122 °F (-2550 °C)	
Ambient Air Temperature For Storage	-58176 °F (-5080 °C)	
Operating Altitude	6561.68 ft (2000 m) without derating	
Flame Retardance	V1 conforming to UL 94	
	Requirement 2 conforming to NF F 16-101	
	Requirement 2 conforming to NF F 16-102	
Mechanical Robustness	Vibrations contactor open2 Gn, 5300 Hz IEC 60068-2-6	
	Vibrations contactor closed4 Gn, 5300 Hz IEC 60068-2-6	
	Shocks contactor open10 Gn for 11 ms IEC 60068-2-27	
	Shocks contactor closed15 Gn for 11 ms IEC 60068-2-27	

# Ordering and shipping details

Category	US10I1222371	
Discount Schedule	0112	
Gtin	3389118078819	
Returnability	No	
Country Of Origin	FR	

### **Packing Units**

Jnit Type Of Package 1	PCF	

Number Of Units In Package 1	1
Package 1 Height	2.56 in (6.5 cm)
Package 1 Width	2.56 in (6.5 cm)
Package 1 Length	1.97 in (5 cm)
Package 1 Weight	6.42 oz (182 g)

# **Contractual warranty**

Warranty 18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Compliant	
EU RoHS Declaration	
China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)	
Product Environmental Profile	
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
End of Life Information	
WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov	