

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Range of product	TeSys
Device short name	GS1AM
Product or component type	Auxiliary contact
Contact application	O and I position signalling
Contacts type and composition	1 C/O
Contact operation	Early-break
[I _{th}] conventional free air thermal current	16 A at 104 °F (40 °C)
[I _e] rated operational current	12 A at 24 V DC-13 2 A at 440 V AC-15 2 A at 48 V DC-13 3 A at 400/415 V AC-15 4 A at 230 V AC-15 5 A at 127 V AC-15 0.4 A at 220 V DC-13 0.6 A at 110 V DC-13

Complementary

Mechanical durability	1000000 cycles
Electrical durability	30000 cycles on AC-15
Product compatibility	GS
Line Rated Current	315 A 100 A 125 A 50 A 60 A 63 A 400 A 200 A 250 A 160 A
Fuse type	NFC BS DIN
Type of operating handle	Direct right side
Product weight	0.05 lb(US) (0.023 kg)

Ordering and shipping details

Category	18402 - WORLD SERVICE PARTS(CONTROL ACCESS)
Discount Schedule	CP10
GTIN	003389110563214
Nbr. of units in pkg.	1
Package weight(Lbs)	5.0000000000000003E-2
Returnability	N
Country of origin	FR

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------