Product data sheet

Specifications





Switch disconnector fuse, TeSys GS, 3P, 30A, fuse type UL, size J

GS2EU3N

Product availability: Stock - Normally stocked in distribution facility

Price*: 260.00 USD

Main

Range	TeSys
Product Name	TeSys GS
Device Short Name	GS2EU
Product Or Component Type	Switch-disconnector-fuse
Poles Description	3P
Protected Poles Description	3t
Contacts Type And Composition	3 NO
[Ith] Conventional Free Air Thermal Current	30 A (at 104 °F (40 °C))
[le] Rated Operational Current	30 A
Fuse Type	UL
Fuse Size	J
Network Type	DC AC
Network Frequency	50/60 Hz

Complementary

Type Of Operating Handle	External frontal
Mounting Support	Rail Plate
[Ui] Rated Insulation Voltage	750 V
[Uimp] Rated Impulse Withstand Voltage	8 kV
Rated Operational Power In W	15 kW 400 V 18.5 kW 500 V 25 kW 690 V
Short-Circuit Withstand	17.6 kA
Mechanical Durability	10000 cycles
Electrical Durability	6000 cycles
Connections - Terminals	Power circuit lugs-ring terminals 0.000.02 in² (213 mm²)
Tightening Torque	Power circuit 58.41 lbf.in (6.6 N.m)

Environment

Standards	UL98	
	CSA C22 2 No 4	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ip Degree Of Protection	IP20 IEC 60529 with terminal cover)
Ambient Air Temperature For Operation	-4158 °F (-2070 °C)
Ambient Air Temperature For Storage	-40176 °F (-4080 °C)
Fire Resistance	1760 °F (960 °C) body
Height	5.35 in (136 mm)
Width	5.88 in (149.3 mm)
Depth	4.84 in (123 mm)

Ordering and shipping details

Category	US10I1122640
Discount Schedule	0111
Gtin	3606480618529
Returnability	Yes
Country Of Origin	TN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.38 in (16.2 cm)
Package 1 Width	6.81 in (17.3 cm)
Package 1 Length	7.09 in (18.0 cm)
Package 1 Weight	4.63 lb(US) (2.1 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

California Proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Circularity Profile	End of Life Information
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Reach Regulation	REACh Declaration