


CA3KN317ED

TeSys K control relay - 3 NO + 1 NC - ≤ 690 V -
48 V DC standard coil

Price* : 49.20 USD



⚠ Discontinued

CA3KN317ED has not been replaced. Please contact your customer care center for more information.

Main

Range	TeSys
Product name	TeSys CAK
Product or component type	Control relay
Device short name	CA3K
Contactor application	Control circuit
Utilisation category	AC-15 DC-13
Pole contact composition	3 NO + 1 NC
System Voltage	≤ 690 V ≤ 400 Hz
Control circuit type	DC standard
[Uc] control circuit voltage	48 V DC

Complementary

[Ith] conventional free air thermal current	10 A at ≤ 122 °F (50 °C)
Irms rated making capacity	110 A conforming to IEC 60947
Associated fuse rating	10 A gG conforming to IEC 60947 10 A gG conforming to VDE 0660
[Ui] rated insulation voltage	600 V conforming to CSA C22.2 No 14 690 V conforming to BS 5424 690 V conforming to IEC 60947 750 V conforming to VDE 0110 group C
Mounting support	Plate Rail
Connections - terminals	Faston terminals 1 6.35 mm Faston terminals 2 2.8 mm
Control circuit voltage limits	0.8...1.15 U _c at 122 °F (50 °C) operational 0.1...0.75 U _c at 122 °F (50 °C) drop-out
Operating time	10 ms coil de-energisation and NO opening 15 ms coil de-energisation and NC closing 25...35 ms coil energisation and NC opening 30...40 ms coil energisation and NO closing
Mechanical durability	20 Mcycles
Operating rate	10000 cyc/h
Immunity to microbreaks	2 ms

Inrush power in W	3 W at 68 °F (20 °C)
Hold-in power consumption in W	3 W at 68 °F (20 °C)
Heat dissipation	3 W
Minimum switching voltage	17 V
Minimum switching current	5 mA
Non overlap distance	0.02 in (0.5 mm)
Insulation resistance	> 10 MOhm
Height	2.28 in (58 mm)
Width	1.77 in (45 mm)
Depth	2.24 in (57 mm)
Product weight	0.5 lb(US) (0.225 kg)

Environment

Standards	BS 5424 IEC 60947 VDE 0660 NF C 63-140
Product certifications	CSA UL
Protective treatment	TC conforming to IEC 60068
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-58...176 °F (-50...80 °C)
Operating altitude	6561.68 ft (2000 m) without derating
Flame retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102
Mechanical robustness	Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6 Vibrations contactor open 2 Gn, 5...300 Hz IEC 60068-2-6 Shocks contactor open 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed 15 Gn for 11 ms IEC 60068-2-27

Ordering and shipping details

Category	22371 - RELAYS, CONTROL
Discount Schedule	I12
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------