


# Product data sheet

Specifications



Auxiliary contact block, TeSys DF, 2NC, 5A, disconnecter, signalling contact, instantaneous

DF14AM2

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 31.50 USD

## Main

Range	TeSys
Device Short Name	DF14
Product Or Component Type	Auxiliary contact block
Auxiliary Contacts Operation	Instantaneous
Pole Contact Composition	2 NC
Connections - Terminals	Faston connector

## Complementary

Range Compatibility	TeSys TeSys DF
[Ui] Rated Insulation Voltage	250 VAC
[Ue] Rated Operational Voltage	24...240 V AC AC-15 24...240 V DC DC-13
[Ith] Conventional Free Air Thermal Current	5 A
Minimum Switching Current	30 mA
Minimum Switching Voltage	10 V
Net Weight	0.06 lb(US) (0.029 kg)

## Environment

Ambient Air Temperature For Operation	-4...140 °F (-20...60 °C)
Ambient Air Temperature For Storage	-40...176 °F (-40...80 °C)

## Ordering and shipping details

Category	US10CP121714
Discount Schedule	0CP1
Gtin	3389119407557
Returnability	No
Country Of Origin	FR

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	1.18 in (3.0 cm)
Package 1 Length	3.11 in (7.9 cm)
Package 1 Weight	0.60 oz (17.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	120
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	6.07 lb(US) (2.753 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability





**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
<b>Reach Regulation</b>	<a href="#">REACH Declaration</a>
<b>Eu Rohs Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>China Rohs Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Weee</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
<b>California Proposition 65</b>	WARNING: Cancer - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>