Product data sheet

Specification





Fuse carrier, TeSys DF, 3P, 25A, 400VAC, fuse size 8.5x31.5mm

DF83

! Discontinued on: May 5, 2023

Product availability: Stock - Normally stocked in distribution facility

Main

| Range | TeSys |
|--|--|
| Product Name | TeSys DF |
| Product Or Component Type | Fuse carrier |
| Device Short Name | DF8 |
| Product Compatibility | DF2BA fuse cartridge DF2BN fuse cartridge |
| Poles Description | 3P |
| Fuse Size | 8.3 x 31.5 mm |
| Fuse Type | , aM , gG |
| Control Type | Toggle padlockable |
| Utilisation Category | AC-20B IEC 60947-3 |
| [Ue] Rated Operational Voltage | 400 V AC |
| [le] Rated Operational Current | 25 A 400 V AC |
| [Ith] Conventional Free Air Thermal Current | 25 A 68 °F (20 °C) |
| [Ui] Rated Insulation Voltage | 500 V AC |
| [Uimp] Rated Impulse Withstand Voltage | 6 kV |
| Overvoltage Category | III |
| Short-Circuit Withstand | 20 kA 400 V IEC 60947-3 |
| Power Dissipation In W | 2.5 W maximum power dissipation by fuse |

Complementary

| Standards | EN/IEC 60947-3 EN/IEC 60269-2 |
|-------------------------|---|
| Product Certifications | IEC EAC DNV-GL |
| Mounting Support | 35 mm symmetrical DIN rail |
| Mounting Position | Vertical +/- 23°) |
| Connections - Terminals | screw clamp terminals 1 0.000.02 in ² (116 mm ²)rigid screw clamp terminals 2 0.000.01 in ² (16 mm ²)rigid screw clamp terminals 1 0.000.02 in ² (116 mm ²)flexible with or without screw clamp terminals 2 0.000.01 in ² (16 mm ²)flexible with or without |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Tightening Torque | 19.47 lbf.in (2.2 N.m) PZ2 19.47 lbf.in (2.2 N.m) flat Ø 5.5 mm |
|-------------------|--|
| Height | 3.13 in (79.5 mm) |
| Width | 2.07 in (52.5 mm) |
| Depth | 2.40 in (61 mm) |
| Net Weight | 0.28 lb(US) (0.126 kg) |
| Quantity Per Set | Set of 4 |

Environment

| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) | |
|---------------------------------------|---|--|
| Ambient Air Temperature For Operation | -40158 °F (-4070 °C) with derating above 20°C | |
| Operating Altitude | 06561.68 ft (02000 m) without derating | |
| Ip Degree Of Protection | IP20 | |
| Pollution Degree | 3 | |
| Fire Resistance | e Resistance 1760 °F (960 °C) IEC 60695-2-1 | |
| Compatibility Code | DF8 | |

Ordering and shipping details

| Category | 21714-DF FUSEHOLDERS |
|-------------------|----------------------|
| Discount Schedule | CP1 |
| Gtin | 3389119407137 |
| Returnability | No |
| Country Of Origin | FR |

Packing Units

| r aciming Critico | |
|------------------------------|-------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.46 in (8.8 cm) |
| Package 1 Width | 2.05 in (5.2 cm) |
| Package 1 Length | 2.52 in (6.4 cm) |
| Package 1 Weight | 5.01 oz (142 g) |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 4 |
| Package 2 Height | 2.68 in (6.8 cm) |
| Package 2 Width | 3.35 in (8.5 cm) |
| Package 2 Length | 8.74 in (22.2 cm) |
| Package 2 Weight | 20.04 oz (568 g) |
| Unit Type Of Package 3 | S03 |
| Number Of Units In Package 3 | 64 |
| Package 3 Height | 11.81 in (30 cm) |
| Package 3 Width | 11.81 in (30 cm) |
| Package 3 Length | 15.75 in (40 cm) |

Package 3 Weight

21.25 lb(US) (9.641 kg)

Contractual warranty

Warranty

Apr 25, 2024

18 months

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| ⊘ | Toxic Heavy Metal Free | |
| ② | Mercury Free | |
| | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | No need of specific recycling operations Circularity Profile |
| California Proposition 65 | WARNING: Cancer - www.P65Warnings.ca.gov |