## **Product data sheet**

Specifications





# Auxiliary contact block, TeSys GV7, 1 C/O standard

GV7AE11

! Discontinued on: May 17, 2022

Product availability: Non-Stock - Not normally stocked in distribution facility

## ! Discontinued

### Main

Range	TeSys
Device Short Name	GV7AE
Product Or Component Type	Auxiliary contact block
Device Application	Signalling
Range Compatibility	TeSys TeSys GV5 motor circuit breaker TeSys TeSys GV6 motor circuit breaker TeSys TeSys GV7 motor circuit breaker
Auxiliary Contact Composition	1 C/O
Auxiliary Contacts Type	Standard contacts
Auxiliary Contacts Operation	Instantaneous
[Ith] Conventional Free Air Thermal Current	6 A IEC 60947-5-1
[Ue] Rated Operational Voltage	<= 690 V AC 50/60 Hz <= 250 V DC
[le] Rated Operational Current	6 A AC-12 Ue: <= 690 V IEC 60947-5-1 6 A AC-15 Ue: <= 48 V IEC 60947-5-1 5 A AC-15 Ue: 110127 V IEC 60947-5-1 4 A AC-15 Ue: 230240 V IEC 60947-5-1 3 A AC-15 Ue: 380440 V IEC 60947-5-1 0.1 A AC-15 Ue: 660690 V IEC 60947-5-1 2.5 A DC-12 Ue: <= 48 V IEC 60947-5-1 0.8 A DC-12 Ue: 110 V IEC 60947-5-1 0.3 A DC-12 Ue: 250 V IEC 60947-5-1 1 A DC-14 Ue: <= 24 V IEC 60947-5-1 0.5 A DC-14 Ue: 48 V IEC 60947-5-1 0.2 A DC-14 Ue: 250 V IEC 60947-5-1 0.2 A DC-14 Ue: 250 V IEC 60947-5-1
Minimum Switching Current	5 mA
Minimum Switching Voltage	17 V

### Complementary

[Ui] Rated Insulation Voltage	690 V IEC 60947-1	
Protection Type	GG fuse 10 A maximum GB2CB circuit breaker 10 A maximum	
Mechanical Durability	50000 cycles	
Mounting Location	Inside the circuit breaker	
Connections - Terminals	screw clamps terminals 1 0.00 in² (1.5 mm²)flexible with cable end screw clamps terminals 1 0.00 in² (1.5 mm²)flexible without cable end screw clamps terminals 1 0.00 in² (1.5 mm²)rigid	
Net Weight	0.03 lb(US) (0.015 kg)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Ordering and shipping details

Category	US10I1122366	
Discount Schedule	ule 0l11	
Gtin	3389110566901	
Returnability	No	
Country Of Origin	FR	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
	Mercury Free	
<b>Ø</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Environmental Disclosure</b>	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov