


Product data sheet

Specifications



Cable end, Lineryg TR cable ends, single conductor, blue, 16mm², for insulated cable, long size, 10 sets of 100

DZ5CA163D

⚠ Discontinued

Main

Range Of Product	Lineryg
Product Or Component Type	Cable end
Cable End Size	Long
Standards	DIN 46228-4
Type Of Packing	Bag
Quantity Per Set	Set of 100
Cable Cross Section	0.02 in ² (16 mm ²)

Complementary

Cable End Type	Single conductor
Additional Information	For additional marker tag holder
Color	Blue
Bezel Material	Halogen-free plastic
Tube Material	Copper ISO 1337
Number Of Cables	1
Awg Gauge	AWG 6
Bezel Size	Ø 9.6 mm
Tube Diameter	0.24 in (6.2 mm)
Length	1.10 in (28 mm)
Tube Length	0.71 in (18 mm)
Cad Overall Depth	1.10 in (28 mm)
Net Weight	0.22 lb(US) (0.1 kg)

Environment

Ambient Air Temperature For Operation	-4...221 °F (-20...105 °C)
---------------------------------------	----------------------------

Ordering and shipping details

Category	22621-IEC PANEL ACCESSORIES
Discount Schedule	I
Gtin	3389110211214
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.16 in (0.400 cm)
Package 1 Width	0.16 in (0.400 cm)
Package 1 Length	0.55 in (1.400 cm)
Package 1 Weight	0.00 oz (0.100 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	100
Package 2 Height	0.79 in (2.000 cm)
Package 2 Width	4.72 in (12.000 cm)
Package 2 Length	5.91 in (15.000 cm)
Package 2 Weight	3.07 oz (87.000 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	1500
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	5.91 in (15.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	3.30 lb(US) (1.498 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations