

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 43,721.00 USD



### Main

Range of product	AccuSine
Product name	AccuSine PFV+
Product or component type	Electronic VAR controller

### Complementary

Network type	3P
Network configuration	3 or 4 wires
Motor Voltage	380...480 V AC
Network frequency	50/60 Hz auto-sensing (+/- 3 %)
Maximum permissible voltage	1.1 x Un
RMS output current rating	120 A
Reactive power rating	100 kvar at 480 V AC (highest nominal voltage) at 50/60 Hz
Operating mode	Power factor correction Mains current balancing Volt-var support
Installation location	Indoor
Enclosure mounting	Wall mounted
Protection type	Without protection
Heat dissipation	Rear plenum with forced ventilation for high heat flow
Electromagnetic compatibility	Conducted EMC class A conforming to EN 61000-6-4
Accessibility for operation	Front
Location of connection	Bottom

### Environment

Enclosure degree of protection	IP00
Environmental characteristic	Operating: 3C2 conforming to IEC 60721-3-3

Operating: 3S2 conforming to IEC 60721-3-3  
 Storage: 3C3 conforming to IEC 60721-3-3  
 Storage: 3S3 conforming to IEC 60721-3-3

Operating altitude	<= 3280.84 ft (1000 m) (derate : 1 % per 100 m above 1000 m)
Ambient air temperature for operation	32...122 °F (0...50 °C) maximum: with current derating of 2 % per °C over 40°C 32...104 °F (0...40 °C)
Relative humidity	0...95 %
PCBA protection	Conformal coated
Standards	EN 60439-1 EN 61000-6-4 UL 508 CSA C22.2 No 14 UL 60947-1 CSA C22.2 No 60947-1-07
Product certifications	ABS CE cULus RCM DNV-GL
Ambient air temperature for storage	-4...140 °F (-20...60 °C)
Product weight	242.51 lb(US) (110 kg)
Height	55.12 in (1400 mm)
Width	16.57 in (421 mm)
Depth	15.12 in (384 mm)
Colour	Light grey (RAL 7035)

### Ordering and shipping details

Category	00089 - ACTIVE FILTERS
Discount Schedule	DE2C
GTIN	003606480851551
Nbr. of units in pkg.	1
Package weight(Lbs)	368.17000000000002
Returnability	N
Country of origin	US

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1506 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available

### Contractual warranty

Warranty period	18 months
-----------------	-----------