





## Circuit breaker, PowerPacT H, 125A, 3 pole, 600VAC, 14kA, I-Line, thermal magnetic, 80%, ABC

HDA36125

Product availability: Stock - Normally stocked in distribution facility

Price\*: 2,730.00 USD

### Main

Range	PowerPact	
Product Name	PowerPact H	
Product Or Component Type	Circuit breaker	
Device Application	Distribution	

### Complementary

Line Rated Current 125 A		
Number Of Poles	3P	
Protected Poles Description	3t	
Control Type	Toggle	
Breaking Capacity Code	D	
Breaking Capacity	25 kA 240 V AC 50/60 Hz UL 489 18 kA 480 V AC 50/60 Hz 14 kA 600 V AC 50/60 Hz 20 kA 250 V DC	
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz IEC 60947-3	
Network Frequency	50/60 Hz	
[Ics] Rated Service Breaking Capacity	25 kA 220/240 V AC 50/60 Hz IEC 60947-2 18 kA 380/440/415 V AC 50/60 Hz IEC 60947-2 14 kA 500/525 V AC 50/60 Hz IEC 60947-2 20 kA 250 V DC IEC 60947-2 20 kA 500 V DC IEC 60947-2	
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2	
Trip Unit Technology	Thermal-magnetic	
Magnetic Tripping Current	1700 A	
Magnetic Hold Current	900 A	
Continuous Current Rating	80 %	
[Ui] Rated Insulation Voltage	750 V IEC 60947-2	
Suitability For Isolation	Yes IEC 60947-2	
Utilisation Category	n Category Category A	
Awg Gauge	AWG 14AWG 3/0 aluminium/copper terminal	
Local Signalling	Switched off (OFF) 1 trip indicator green)	
Mounting Mode	I-Line bracket)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mounting Support	Bracket	
Electrical Connection	I-Line connection, line Lugs, load	
Terminal Identifier	AL150HD	
Mounting Height	4.5 in (114.30 mm)	
Tightening Torque	44.25 lbf.in (5 N.m) 0.000.01 in² (2.56 mm²) (AWG 14AWG 10) 123.91 lbf.in (14 N.m) 0.020.15 in² (1095 mm²) (AWG 8AWG 3/0)	
Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in)	
Power Wire Stripping Length	0.63 in (16 mm)	
Color	Black	
Height	6.42 in (163 mm)	
Width	4.09 in (104 mm)	
Depth	3.39 in (86 mm)	
Net Weight 4.85 lb(US) (2.2 kg)		
Quantity Per Set	1	
Phase Connection	ABC	
Communication Interface	nunication Interface Modbus Ethernet	
Circuit Breaker Application HACR rated		

### **Environment**

Quality Labels	CE
Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2
Product Certifications	UL CSA NOM
Ip Degree Of Protection	Front cover IP40 IEC 60529
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	< 6561.68 ft (2000 m) without derating 5000 m with derating

# Ordering and shipping details

Category	US10DE2011112	
Discount Schedule	0DE2	
Gtin	785901419990	
Returnability	Yes	
Country Of Origin	CA	

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	6.10 in (15.494 cm)	
Package 1 Width	8.50 in (21.59 cm)	
Package 1 Length	15.00 in (38.1 cm)	
Package 1 Weight	5.46 lb(US) (2.475 kg)	
Unit Type Of Package 2	PAL	
Number Of Units In Package 2	100	
Package 2 Height	36.00 in (91.44 cm)	
Package 2 Width	40.00 in (101.6 cm)	
Package 2 Length	48.00 in (121.92 cm)	
Package 2 Weight	545.60 lb(US) (247.48 kg)	

# **Contractual warranty**

Warranty 18 months

# Sustainability Green Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov