

Product data sheet

Specifications



Electronic VAR control - 300 A 380..480 V AC - IP00 enclosure

EVCP300D5IP00

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 141,474.00 USD

Main

Range Of Product	AccuSine
Product Name	AccuSine PFV+
Product Or Component Type	Electronic VAR controller

Complementary

Network Type	3P
Network Configuration	3 or 4 wires
Network Rated Voltage	380...480 V AC
Input Frequency	50/60 Hz +/- 3 % auto-sensing
Maximum Permissible Voltage	1.1 x Un
Rms Output Current Rating	300 A
Reactive Power Rating	249 kvar 480 V AC 50/60 Hz
Operating Mode	Mains current balancing Power factor correction
Installation Location	Indoor
Enclosure Mounting	Wall mounted
Protection Type	Without protection
Heat Dissipation	Rear plenum with forced ventilation for high heat flow
Electromagnetic Compatibility	Conducted EMC, class A EN 61000-6-4
Accessibility For Operation	Front
Location Of Connection	Bottom

Environment

Enclosure Degree Of Protection	IP00
Environmental Characteristic	Operating 3C2 IEC 60721-3-3 Operating 3S2 IEC 60721-3-3 Storage 3C3 IEC 60721-3-3 Storage 3S3 IEC 60721-3-3
Operating Altitude	<= 3280.84 ft (1000 m) 1 % per 100 m
Ambient Air Temperature For Operation	32...104 °F (0...40 °C) 32...122 °F (0...50 °C) maximum with current derating of 2 % per °C
Relative Humidity	0...95 %
Pcba Protection	Conformal coated

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 508 CSA C22.2 No 14 EN 61000-6-4 UL 60947-1 EN 60439-1 CSA C22.2 No 60947-1-07
Product Certifications	CE DNV-GL ABS RCM cULus
Ambient Air Temperature For Storage	-4...140 °F (-20...60 °C)
Net Weight	485.02 lb(US) (220 kg)
Height	61.42 in (1560 mm)
Width	22.91 in (582 mm)
Depth	17.24 in (438 mm)
Color	Light gray RAL 7035)

Ordering and shipping details

Category	US1DE2C00089
Discount Schedule	DE2C
Gtin	3606480851575
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	27.76 in (70.5 cm)
Package 1 Width	29.02 in (73.7 cm)
Package 1 Length	68.23 in (173.3 cm)
Package 1 Weight	582.02 lb(US) (264.0 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	