# Product data sheet

Specifications



## Transformer, dry type, DOE 2016, 112.5kVA, 3 phase, 240V delta primary, 208Y/120V secondary, 21K, 150C rise

EX112T239H

() Discontinued on: Nov 22, 2021

# Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range Of Product	Square D
Product Or Component Type	Transformer
Device Short Name	DOE 2016
Transformer Type	Energy efficient
Device Application	Low voltage electrical distribution

### Complementary

Box Number	21K
Phase	3 phase
Rated Operational Power In Va	112.5 kVA
Network Frequency	60 Hz
Type Of Cooling	Natural convection
Primary Voltage	240 V delta
Number Of Tap-Offs	1 5 % FCAN 2 5 % FCBN
Secondary Voltage	208Y/120 V
Coil Material	Aluminium
Basic Imp Level (Bil)	10 kV
Temperature Rise	150 °C 220 °C insulated
Doe Efficiency	98.83 % at 35 % load factor , 167 °F (75.0 °C)
Sound Level	47 dB 6 dB NEMA ST-20
%lz	5.00 %
%lx	0.0421 %
X/R Ratio	1.61
Let Through Current	6.3 kA
Transformer Losses	171.0 no load (core loss) 2943.0 load loss (coil loss)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Transformer Btu/Hr	860,1918127137359 16.6 %
	1211.097151125 25 %
	3093.9597584999997 50 %
	6232.064104124999 75 %
	10625.410188 100 %
	10025.410100 100 %
Height	45.98 in (1168 mm)
Depth	24.02 in (610 mm)
Width	31.30 in (795 mm)
Net Weight	865.01 lb(US) (392.36 kg)
Mounting Support	Floor
	Floor, with 7400FMB
	Ceiling, with 7400CMB21K
Degree Of Protection	UL type 1
	UL type 2, with 7400DS21K
	UL type 3R, with 7400WS21K
Electrical Connection	4 Hole Nema Pad primary 0.44 in (11.1 mm)
	4 Hole Nema Pad secondary 0.44 in (11.1 mm)
	6 Hole Nema Pad sec - XO 0.44 in (11.1 mm)

#### Environment

Ambient Air Temperature For Operation	104 °F (40 °C)
Average Ambient Air Temperature For Operation	30 °C
Standards	UL 1561 CSA C22.2 No 47 NEMA ST-20

## Ordering and shipping details

_		
Category	US1PE2X16500	
Discount Schedule	PE2X	
Gtin	785901753759	
Returnability	No	
Country Of Origin	US	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	46.10 in (117.1 cm)
Package 1 Width	26.26 in (66.7 cm)
Package 1 Length	33.82 in (85.9 cm)
Package 1 Weight	965.00 lb(US) (437.717 kg)

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance


Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product


#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

#### **Dimensions Drawings**

#### Approximate Dimensions





in. (mm)