Product data sheet

Specification





gearbox straight teeth GBX, Lexium, 60mm, reduction 20:1, 12arc.min, 44N.m

GBX060020K

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 539.12 USD

Main

Range Compatibility	Lexium 62 ILM					
	Lexium 52					
	Lexium ILS					
	Lexium 62					
	Lexium ILA					
	Lexium 28					
	Lexium SD3					
	Lexium ILE					
	Lexium 32					
Product Or Component Type	Planetary gearbox					
Gear Box Type	Straight teeth					
Device Short Name	GBX					
Product Compatibility	BSH 2.17 in (55 mm), 1					
	BSH 2.17 in (55 mm), 2					
	BRS3					
	ILE 2.60 in (66 mm), 1					
	ILE 2.60 in (66 mm), 2					
	ILA 2.24 in (57 mm), 1					
	ILA 2.24 in (57 mm), 2					
	ILS 2.24 in (57 mm), 1					
	ILS 2.24 in (57 mm), 2					
	ILS 2.24 in (57 mm), 3					
	BCH2 2.36 in (60 mm), 1					
	SH3					
	MH3					
	ILM					
Gearbox External Diameter	2.36 in (60 mm)					
Reduction Ratio	20:1					

Complementary

Maximum Torsional Backlash	12 arc.min					
Torsional Rigidity	2.5 N.m/arcmin					
Housing Colour	Black					
Housing Material	Black anodized aluminium					
Shaft Material	C 45					
Additional Information	Lubricated for life					
Service Life In Hours	30000 h 100 rpm 86 °F (30 °C)					
Mounting Position	Any position					
Efficiency	94 %					
Maximum Radial Force Fr	340 N 100 rpm, force applied at mid-distance from output shaft during 30000 hour at 30 $^{\circ}\text{C}$					

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Maximum Axial Force Fa	450 N 100 rpm, during 30000 hour at 30°C				
Moment Of Inertia	0.075 kg.cm²				
Continuous Output Torque	389.43 lbf.in (44 N.m) 100 rpm 86 °F (30 °C)				
Maximum Output Torque	619.55 lbf.in (70 N.m) 100 rpm 86 °F (30 °C)				
Net Weight	2.43 lb(US) (1.1 kg)				
Input Diameter	0.55 in (14.0 mm)				

Environment

Noise Level	58 dB 1 m, no-load			
Ip Degree Of Protection	Shaft output IP54			
Ambient Temperature For	-13194 °F (-2590 °C)			

Ordering and shipping details

Category	US1PC5318283
Discount Schedule	PC53
Gtin	3606480388262
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7.000 cm)
Package 1 Width	2.68 in (6.800 cm)
Package 1 Length	5.71 in (14.500 cm)
Package 1 Weight	2.23 lb(US) (1.013 kg)
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	23.57 lb(US) (10.691 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance




Certifications & Standards

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.				
Environmental Disclosure	Product Environmental Profile				
Circularity Profile	No need of specific recycling operations				
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov				

GBX060020K

Dimensions Drawings

Dimensions with Servo Motor Adaptation Kit



- (1) GBK adaptation kit
- (2) GBK adaptation kit related dimensions a1, c, Ø6, Ø7, Ø8 depend on the gearbox and servo motor combination
- Ø8 shaft end adaptor in case motor shaft diameter is smaller than gearbox input coupling diameter

Values in mm

		•								
a2	а3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
67.5	35	30	2.5	16	5	60	40 h7	14 h7	M5 x 8	52

Values in in.

a2	а3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
2.66	1.38	1.18	0.10	063	0.19	2.36	1.57 h7	0.55 h7	M5 x 0.31	2.05