





PowerPact

PowerPact H

Circuit breaker, PowerPacT H, 15A, 3 pole, 600VAC, 50kA, lugs, thermal magnetic, 80%

HLL36015

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,849.00 USD

Main Range

Product Name

Product Or Component Type	Circuit breaker	
Device Application	Distribution	
Complementary		
Line Rated Current	15 A	
Number Of Poles	3P	
Protected Poles Description	3t	
Control Type	Toggle	
Breaking Capacity Code	L	
Breaking Capacity	125 kA 240 V AC 50/60 Hz UL 489 100 kA 480 V AC 50/60 Hz UL 489 50 kA 600 V AC 50/60 Hz UL 489 20 kA 250 V DC UL 489 50 kA 500 V DC UL 489	
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz IEC 60947-3	
Network Frequency	50/60 Hz	
[Ics] Rated Service Breaking Capacity	125 kA 220/240 V AC 50/60 Hz IEC 60947-2 100 kA 380/440/415 V AC 50/60 Hz IEC 60947-2 50 kA 500/525 V AC 50/60 Hz IEC 60947-2 20 kA 250 V DC IEC 60947-2 20 kA 500 V DC IEC 60947-2	
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2	
Trip Unit Technology	Thermal-magnetic	
Magnetic Tripping Current	750 A	
Magnetic Hold Current	350 A	
Continuous Current Rating	80 %	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

AWG 14...AWG 3/0 aluminium/copper terminal

Switched off (OFF) 1 trip indicator green)

750 V IEC 60947-2

Yes IEC 60947-2

Category A

[Ui] Rated Insulation Voltage

Suitability For Isolation

Utilisation Category

Awg Gauge

Local Signalling

Mounting Mode	Unit mount lug)	
Mounting Support	Lug	
Electrical Connection	Lugs, line Lugs, load	
Terminal Identifier	AL150HD	
Tightening Torque	44.25 lbf.in (5 N.m) 0.000.01 in² (2.56 mm²) (AWG 14AWG 10) 123.91 lbf.in (14 N.m) 0.020.15 in² (1095 mm²) (AWG 8AWG 3/0)	
Number Of Slots	auxiliary switch OF plug-in) alarm switch SD plug-in) overcurrent trip switch SDE plug-in) voltage release MN or MX plug-in)	
Power Wire Stripping Length	0.63 in (16 mm)	
Color	Black	
Height	6.42 in (163 mm)	
Width	4.09 in (104 mm)	
Depth	3.39 in (86 mm)	
Net Weight	4.85 lb(US) (2.2 kg)	
Quantity Per Set	1	
Communication Interface	Modbus Ethernet	
Circuit Breaker Application	HACR rated	

Environment

Quality Labels	CE
Standards	UL
	CSA
	NEMA
	NOM-003-SCFI-2000
	IEC 60947-2
Product Certifications	UL
	CSA
	NOM
Ip Degree Of Protection	Front cover IP40 IEC 60529
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	< 6561.68 ft (2000 m) without derating
	5000 m with derating

Ordering and shipping details

Category	US10DE201120
Discount Schedule	0DE2
Gtin	785901598879
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE		

Number Of Units In Package 1	1
Package 1 Height	5.60 in (14.224 cm)
Package 1 Width	7.60 in (19.304 cm)
Package 1 Length	8.70 in (22.098 cm)
Package 1 Weight	4.11 lb(US) (1.865 kg)

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration Compliant with Exemptions	
Eu Rohs Directive		
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End of Life Information	
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	