


GS1ANT22

TeSys GS - auxiliary contact - 2 NO+2 NC - front/
right hand side - 50...400 A



⚠ Discontinued

GS1ANT22 has not been replaced. Please contact your customer care center for more information.

Main

Range of product	TeSys
Device short name	GS1AN
Product or component type	Auxiliary contact
Contact application	O, I and test position signalling
Contacts type and composition	2 NO + 2 NC
Contact operation	Instantaneous
[I _{th}] conventional free air thermal current	20 A at 104 °F (40 °C)
[I _e] rated operational current	1 A at 220 V DC-13 10 A at 230 V AC-15 12 A at 127 V AC-15 4 A at 48 V DC-13 6 A at 440 V AC-15 8 A at 400/415 V AC-15 1.2 A at 110 V DC-13

Complementary

Range compatibility	TeSys ,TeSys GS ,fuse-switch disconnecter
Mechanical durability	30000 cycles
Electrical durability	30000 cycles on AC-15
Product compatibility	GS
Line Rated Current	63 A 50 A 60 A 315 A 400 A 100 A 125 A 250 A 200 A 160 A
Fuse type	DIN BS NFC
Type of operating handle	External right side External frontal
Product weight	0.57 lb(US) (0.258 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	22640 - IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	00785901367796
Nbr. of units in pkg.	1
Package weight(Lbs)	0.57000000000000006
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1650 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------