

Product data sheet

Specifications



switch-disconnector fuse body GS1 - TeSys GS - 3 poles - DIN - 250 A

GS1NG3

! Discontinued

Main

Device Short Name	GS1 N
Fuse Type	DIN
Fuse Size	T1
Product Or Component Type	Fuse switch disconnector body
Poles Description	3P
Network Type	DC AC
Type Of Operating Handle	External left side
[Ith] Conventional Free Air Thermal Current	250 A (at 104 °F (40 °C))

Complementary

Network Frequency	50/60 Hz
Mounting Support	Plate Rail
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ie] Rated Operational Current	200 A 440 V 2 poles in series per phase DC-23A 200 A 440 V 2 poles in series per phase DC-23B 250 A 400 V AC-23A 250 A 400 V AC-23B 250 A 500 V AC-23A 250 A 500 V AC-23B 250 A 690 V with terminal cover AC-23A 250 A 690 V with terminal cover AC-23B
Rated Operational Power In W	400 V AC-23A) 400 V AC-23B) 500 V AC-23A) 500 V AC-23B) 690 V AC-23A) 690 V AC-23B)
Making Capacity	2500 A 400 V AC-23B
[Icm] Rated Short-Circuit Making Capacity	100 kA 400 V with protection by gG (gl) fuses 250 kA rating of associated fuses
Breaking Capacity	2000 A 400 V AC-23B)
Mechanical Durability	10000 cycles
Electrical Durability	1000 cycles AC-23A 1000 cycles AC-23B 200 cycles DC-23A 200 cycles DC-23B

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Power circuit bars Power circuit screw terminals 0.15...0.37 in² (95...240 mm²) flexible
Tightening Torque	Power circuit 221.27 lbf.in (25 N.m) bars Power circuit 221.27 lbf.in (25 N.m) screw terminals
Net Weight	7.05 lb(US) (3.2 kg)

Environment

Standards	IEC 60947-3 IEC 60269-2 IEC 60269-1
Product Certifications	LOVAG ASEFA LROS (Lloyds register of shipping)
Protective Treatment	TH
Ip Degree Of Protection	IP20 IEC 60529 with terminal cover)
Fire Resistance	1562 °F (850 °C) fuse cover IEC 60695-2-1 1760 °F (960 °C) body IEC 60695-2-1

Ordering and shipping details

Category	18402-WORLD SERVICE PARTS(CONTROL ACCESS)
Discount Schedule	CP10
Gtin	3389110559613
Returnability	No
Country Of Origin	FR

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.p65warnings.ca.gov
