

Product data sheet

Specifications



Panel PC Performance - Flash Disk - 19" - DC - 0 slot - 500 I/O - fan

HMIPPF9D07F1

⚠ Discontinued on: Jun 30, 2016

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

Main

Range Of Product	Harmony iPC
Product Or Component Type	PC panel
Processor Name	Core 2 Duo P8400 2.26 GHz cache 6 MB
Chipset Type	Intel GM45 1.066 GHz
Display Size	19 inch
Display Colour	16 million colours
Luminance	27.87 fc (300 cd/m²)
Video Controller Type	Intel Graphics Media Accelerator (GMA) 4500MHD, 384 MB
Operating System	Windows 7 64 bits Ultimatemulti-language
Software Package	Vijeo Designer run time demo Vijeo Citect client/server, 500 I/O
Bezel Material	Aluminium alloy

Complementary

Terminal Type	Touchscreen display
Data Storage Equipment	>= 60 GB Flash disk SSD MLC 2000000 h
Display Type	Active matrix colour TFT LCD with LED backlight
Display Resolution	1280 x 1024 pixels SXGA
View Angle Horizontal X Vertical	160 x 100°
Touch Panel	Analogue resistive
Memory Type	512 KB SRAM 4 GB RAM DDR3
Type Of Cooling	Fan
Integrated Connection Type	2 Ethernet TCP/IP - RJ45 DVI-I video port - DVI-I COM1 serial link - male SUB-D 9 - RS232C 115 kbit/s) COM2 serial link - male SUB-D 9 - RS232C 115 kbit/s) USB 2.0 type A 480 Mbit/s)front panel 4 USB 2.0 type A 480 Mbit/s)top panel
Port Ethernet	10BASE-T/100BASE-T/1000BASE-T
[Us] Rated Supply Voltage	24 V DC power supply
Supply Voltage Limits	18...30 V
Line Rated Current	6.7 A
Inrush Current	7 A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Power Consumption In W	130 W
Material	Treated steel
Display Material	Polyethylene sheet
Fixing Mode	Enclosure door by fixing kit fasteners included) Panel by fixing kit fasteners included)
Type Of Installation	Indoor
Control Type	ON/OFF push-button equipment ON and OFF) Push-button reset)
Local Signalling	for power LED (multi-colour) for accessing Flash disk SSD (DISK) LED (yellow)
Width	18.90 in (480 mm)
Height	14.96 in (380 mm)
Depth	5.08 in (129 mm)
Cut-Out Dimensions	459.5 (+/- 0.5) x 359.5 (+/- 0.5) x 1.6...10 mm
Net Weight	32.54 lb(US) (14.76 kg)
Main Type	Performance

Environment

Ip Degree Of Protection	IP65 front panel: conforming to EN/IEC 60529
Nema Degree Of Protection	NEMA 4X front panel
Product Certifications	CULus 508 CULus CSA 22-2 No 142 CULus HazLoc Class I Division 2 UL 1604 CULus HazLoc Class I Division 2 ANSI/ISA 12-12-01 CULus HazLoc Class I Division 2 CSA 22-2 No 213 GOST CE C-tick
Pollution Degree	2 EN/IEC 61131-2
Electromagnetic Compatibility	Immunity to electromagnetic emissions, class A EN 55022 Immunity to electromagnetic emissions, class A EN 55011 Immunity to high frequency interference EN/IEC 61131-2 Immunity to high frequency interference EN/IEC 61000-4-x
Ambient Air Temperature For Operation	32...122 °F (0...50 °C) vertical installation UL 508 32...122 °F (0...50 °C) vertical installation EN/IEC 61131-2
Ambient Air Temperature For Storage	-4...140 °F (-20...60 °C) IEC 60068-2-2 test Bb -4...140 °F (-20...60 °C) IEC 60068-2-14 test Na
Relative Humidity	10...85 % EN/IEC 60068-2-78 10...85 % EN/IEC 60068-2-30
Operating Altitude	6561.68 ft (2000 m) EN/IEC 61131-2
Vibration Resistance	1.75 mm 2...9 Hz) continuous EN/IEC 60068-2-6 Fc 3.5 mm 2...9 Hz) intermittently EN/IEC 60068-2-6 Fc 0.5 gn 9...200 Hz) continuous EN/IEC 60068-2-6 Fc 1 gn 9...200 Hz) intermittently EN/IEC 60068-2-6 Fc 1 mm 3...13.2 Hz) continuous EN/IEC 60068-2-6 Fc 0.7 gn 13.2...100 Hz) continuous EN/IEC 60068-2-6 Fc
Shock Resistance	15 gn 11 ms IEC 60068-2-27, Ea tests

Ordering and shipping details

Category	22575-MAGELIS MC3
Discount Schedule	MC3


Gtin	00785901321484
Returnability	No
Country Of Origin	FR

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions Drawings



Dimensions




K : 28 mm / 1.10 in.

Mounting and Clearance


Spacing Requirements

Top, Bottom and Rear Sides	Left and Right Sides
 1 Air out 2 Air in	
x1 > 100 mm (3.93 in.) x2 > 50 mm (1.96 in.) x3 > 10 mm (0.39 in.)	

Mounting Orientation



Panel Cut Dimensions



1 Installation panel

A	B	C
459.5 ± 0.5 mm (18.09 ± 0.02 in.)	359.5 ± 0.5 mm (14.15 ± 0.02 in.)	1.6...10 mm (0.06...0.39 in.)