Product data sheet

Specifications





Touch panel screen, Harmony STO & STU, 3"4 monochrome W/ P/R for Zelio

HMISTO501

! Discontinued on: Dec 2, 2020

! End-of-service on: Dec 28, 2023

① Discontinued - Service only

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony STO & STU	
Product Or Component Type	Touch panel screen	
Software Designation	Vijeo Designer	
Operating System	Harmony	
Processor Name	CPURISC	

Complementary

Display Size	3.4 inch			
Display Type	Backlit monochrome STN LCD			
Background Colour	White, pink and red			
Display Resolution	200 x 80 pixels			
Touch Panel	Analogue			
Backlight Lifespan	10000 hours red 50000 hours pink 50000 hours white			
Brightness	8 levels			
Contrast	16 levels via touch panel			
Character Font	Korean Japanese (ANK, Kanji) Taiwanese (traditional Chinese) Chinese (simplified Chinese) ASCII			
[Us] Rated Supply Voltage	24 V DC +/- 20 %			
Inrush Current	30 A			
Local Signalling for normal operation 1 LED (green)				
Power Consumption In W 5 W				
Number Of Pages	Es Limited by internal memory capacity			
Processor Frequency	333 MHz			
Memory Description	Application memory 16 MB Back up of data 128 kB			

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Integrated Connection Type	1 USB 2.0 type mini B 1 USB 2.0 type A power supply - removable screw terminal block serial link - 9-pin terminal block - RS232C			
Supply	External source			
Realtime Clock	Access to the PLC real-time clock			
Downloadable Protocols	Zelio			
Range Compatibility	Zelio Logic			
Fixing Mode	By 2 spring clips 1.65 mm thick panel			
Enclosure Material	PPT			
Marking	CE			

Environment

Immunity To Microbreaks	3 ms IEC 61000-6-2 FCC Class A UL 508 UL 1604 EN 61131-2				
Standards					
Product Certifications	CE UL Class 1 Division 2 T5 UL Class 1 Division 2 T4A C-tick cULus				
nbient Air Temperature For 32122 °F (050 °C) peration					
Ambient Air Temperature For Storage	-4140 °F (-2060 °C)				
Relative Humidity	090 % without condensation				
Operating Altitude <= 6561.68 ft (2000 m)					
Ip Degree Of Protection IP20 IEC 60529 rear panel) IP65 IEC 60529 front panel)					
Nema Degree Of Protection NEMA 4X front panel (indoor use)					
Shock Resistance	15 gn 11 msIEC 60068-2-27				
Vibration Resistance	+/- 3.5 mm 59 Hz) IEC 60068-2-6 1 gn 9150 Hz) IEC 60068-2-6				
Electromagnetic Compatibility	Resistance to radiated electromagnetic fields - test level: 10 V/m conforming to IEC 61000-4-3				

Ordering and shipping details

Category	US10MC222569		
Discount Schedule	0MC2		
Gtin	3595864127835		
Returnability	No		
Country Of Origin	US		

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.35 in (8.5 cm)

Package 1 Width	5.12 in (13.0 cm)		
Package 1 Length	7.48 in (19.0 cm)		
Package 1 Weight	13.47 oz (382.0 g)		

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Reach Free Of Svhc	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes


Certifications & Standards


Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.				
Circularity Profile	End of Life Information				
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov				

HMISTO501

Dimensions Drawings


Dimensions with Spring Clips





- **(1)** Top
- (2) Front

Dimensions without Spring Clips



- **(1)** Top
- (2) Front
- (3) Right Side


Product data sheet


HMISTO501

Mounting and Clearance


Clearance

in.





Panel Cut-out Dimensions



(1) Panel

A (mm)	A (in.)	B (mm)	B (in.)	C (mm) Spring Clips	C (in.) Spring Clips	R (mm)	R (in.)
+1 105 -0	+0.04 4.13 -0	+1 66 -0	+0.04 2.59 -0	1.5 to 6.0	0.059 to 0.236	2.0 to 3.0	0.078 to 0.118