Product data sheet

Specification





TeSys Deca - auxiliary contact - 2 NO

GVAE20

Product availability: Stock - Normally stocked in distribution facility

Price*: 35.70 USD

Main

Range	TeSys TeSys Deca	
Device Short Name	GVAE	
Product Or Component Type	Auxiliary contact block	
Product Compatibility	GV2L GV3P GV2ME LS1D32 GV3L GV2RT GV2P GV2P	
Mounting Location	Front side	
Pole Contact Composition	2 NO	
Quantity Per Set	Set of 10	

Complementary

[Ui] Rated Insulation Voltage	300 V UL 508 300 V CSA C22.2 No 14 250 V IEC 60947-1
[Ue] Rated Operational Voltage	24240 V AC 2460 V DC
[Ith] Conventional Free Air Thermal Current	2.5 A
Mechanical Durability	100000 cycles
Minimum Switching Current	5 mA
Minimum Switching Voltage	17 V
Protection Type	GG fuse 10 A GB2CB06 circuit breaker 10 A
Rated Operational Power In Va	120 VA 110120 V AC-15 100000 cycles 120 VA 230240 V AC-15 100000 cycles 48 VA 24 V AC-15 100000 cycles 60 VA 48 V AC-15 100000 cycles
Rated Operational Power In W	15 W 48 V DC-13 100000 cycles 24 W 24 V DC-13 100000 cycles 9 W 60 V DC-13 100000 cycles
Tightening Torque	12.39 lbf.in (1.4 N.m) screw clamp terminals
Height	0.43 in (11 mm)
Width	1.77 in (45 mm)
Depth	1.14 in (29 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Net Weight 0.04 lb(US) (0.02 kg)

Environment

Environmental Characteristic	Normal environment	
Product Certifications	UKCA	

Ordering and shipping details

Category	US10I1122367	
Discount Schedule	0111	
Gtin	3389110343465	
Returnability	Yes	
Country Of Origin	CZ	

Packing Units

PCE	
1	
0.63 in (1.600 cm)	
1.97 in (5.000 cm)	
2.36 in (6.000 cm)	
0.67 oz (19.000 g)	
BB1	
10	
2 Height 2.48 in (6.300 cm)	
2.87 in (7.300 cm)	
4.72 in (12.000 cm)	
7.37 oz (209.000 g)	
S02	
220	
5.91 in (15.000 cm)	
11.81 in (30.000 cm)	
Length 15.75 in (40.000 cm)	
9.65 lb(US) (4.377 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
②	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Connections and Schema

GVAE20