Product data sheet

Specifications





Shunt release (MX), TeSys Deca, 24V AC 60Hz

GVAS026

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 81.00 USD

Main

Range	TeSys TeSys Deca
Product Or Component Type	Shunt trip release
Device Short Name	GVAS

Complementary

Complementary	
Range Compatibility	TeSys GV2ME TeSys GV2LE TeSys GV2L TeSys GV2P TeSys GV3L TeSys GV3P TeSys Deca
[Uc] Control Circuit Voltage	24 V AC 60 Hz
Control Circuit Voltage Limits	0.71.1 Un
[Ui] Rated Insulation Voltage	690 V AC IEC 60947-1 600 V AC UL 60947-4-1 600 V AC CSA C22.2 No 60947-4-1
Threshold Tripping Voltage	0.750.2 Un
Inrush Power In Va	14 VA AC
Inrush Power In W	10.5 W
Hold-In Power Consumption In Va	5 VA AC
Hold-In Power Consumption In W	1.6 W
Operating Time	1015 ms IEC 60947-1
On-Load Factor	100 %
Connections - Terminals	screw clamp terminals 1 0.000.00 in ² (12.5 mm ²)solid screw clamp terminals 2 0.000.00 in ² (12.5 mm ²)solid screw clamp terminals 1 0.000.00 in ² (0.752.5 mm ²)flexible without cable end screw clamp terminals 2 0.000.00 in ² (0.752.5 mm ²)flexible without cable end screw clamp terminals 1 0.000.00 in ² (0.751.5 mm ²)flexible with cable end screw clamp terminals 2 0.000.00 in ² (0.751.5 mm ²)flexible with cable end
Tightening Torque	< 1.4 N.m screw clamp terminals
Mechanical Durability	10000 cycles with GV3P and GV3L 30000 cycles with GV2ME and GV2P
Quantity Per Set	Set of 10
Height	3.50 in (89 mm)
Width	0.71 in (18 mm)
Depth	2.60 in (66 mm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Net Weight	0.23 lb(US) (0.105 kg)
Color	Dark grey

Ordering and shipping details

Category	US10I1122367
Discount Schedule	0111
Gtin	3389110343588
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.27 in (8.3 cm)
Package 1 Width	1.42 in (3.6 cm)
Package 1 Length	3.62 in (9.2 cm)
Package 1 Weight	3.95 oz (112.0 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Product data sheet

Connections and Schema

GVAS•••

