# Product data sheet

Specifications



### Safety switch, heavy duty, fusible, 600A, 4 wire, 3 pole, 1 neutral, 200hp, 240VAC/250VDC, NEMA 1

H326N

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 6,519.00 USD

#### Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Fusible disconnect
Factory Installed Neutral	Neutral (factory installed)
Phase	3 phase
Number Of Poles	3
Current Rating	600 A
Voltage Rating	250 V DC 240 V AC
Enclosure Rating	NEMA 1 steel
Motor Power Hp	75 hp at 240 V AC 50-60 Hz for 3 phase motors 200 hp at 240 V AC 50-60 Hz for 3 phase motors 50 hp at 250 V DC

#### Complementary

Short-Circuit Current10 kA for H or K 200 kA for R or JFuse TypeH or K R or JMounting TypeSurfaceElectrical ConnectionLugsWiring Configuration4-wire (3PH + G)Wire SizeAWG 3/0500 kcmil copper or aluminiumTightening Torque375 lbf.in (42.37 N.m) (AWG 3/0500 kcmil)Depth10.13 in (257.30 mm)Width27.63 in (701.80 mm)Height50.25 in (1276.35 mm)Net Weight179.90 lb(US) (81.6 kg)	• •	
R or JMounting TypeSurfaceElectrical ConnectionLugsWiring Configuration4-wire (3PH + G)Wire SizeAWG 3/0500 kcmil copper or aluminiumTightening Torque375 lbf.in (42.37 N.m) (AWG 3/0500 kcmil)Depth10.13 in (257.30 mm)Width27.63 in (701.80 mm)Height50.25 in (1276.35 mm)	Short-Circuit Current	
Electrical Connection Lugs   Wiring Configuration 4-wire (3PH + G)   Wire Size AWG 3/0500 kcmil copper or aluminium   Tightening Torque 375 lbf.in (42.37 N.m) (AWG 3/0500 kcmil)   Depth 10.13 in (257.30 mm)   Width 27.63 in (701.80 mm)   Height 50.25 in (1276.35 mm)	Fuse Туре	
Wiring Configuration4-wire (3PH + G)Wire SizeAWG 3/0500 kcmil copper or aluminiumTightening Torque375 lbf.in (42.37 N.m) (AWG 3/0500 kcmil)Depth10.13 in (257.30 mm)Width27.63 in (701.80 mm)Height50.25 in (1276.35 mm)	Mounting Type	Surface
Wire Size     AWG 3/0500 kcmil copper or aluminium       Tightening Torque     375 lbf.in (42.37 N.m) (AWG 3/0500 kcmil)       Depth     10.13 in (257.30 mm)       Width     27.63 in (701.80 mm)       Height     50.25 in (1276.35 mm)	Electrical Connection	Lugs
Tightening Torque     375 lbf.in (42.37 N.m) (AWG 3/0500 kcmil)       Depth     10.13 in (257.30 mm)       Width     27.63 in (701.80 mm)       Height     50.25 in (1276.35 mm)	Wiring Configuration	4-wire (3PH + G)
Depth     10.13 in (257.30 mm)       Width     27.63 in (701.80 mm)       Height     50.25 in (1276.35 mm)	Wire Size	AWG 3/0500 kcmil copper or aluminium
Width     27.63 in (701.80 mm)       Height     50.25 in (1276.35 mm)	Tightening Torque	375 lbf.in (42.37 N.m) (AWG 3/0500 kcmil)
Height     50.25 in (1276.35 mm)	Depth	10.13 in (257.30 mm)
	Width	27.63 in (701.80 mm)
Net Weight     179.90 lb(US) (81.6 kg)	Height	50.25 in (1276.35 mm)
	Net Weight	179.90 lb(US) (81.6 kg)

#### Environment

Certifications

UL listed file E2875

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

# Ordering and shipping details

Category	US10DE100053
Discount Schedule	0DE1
Gtin	785901451686
Returnability	Yes
Country Of Origin	MX

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.02 in (35.6 cm)
Package 1 Width	27.99 in (71.1 cm)
Package 1 Length	52.01 in (132.1 cm)
Package 1 Weight	175.00 lb(US) (79.379 kg)

### **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

### Certifications & Standards

REACh Declaration
Compliant with Exemptions
China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov