# Product data sheet

Specifications







# Circuit breaker, PowerPacT J, 175A, 3 pole, 600VAC, 25kA, lugs, thermal magnetic, 80%, aux

JJL36175AA

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 5,729.00 USD

#### Main

Range	PowerPact	
Product Name	PowerPact J	
Product Or Component Type	Circuit breaker	
Device Application	Distribution	

### Complementary

Complementary	
Line Rated Current	175 A
Number Of Poles	3P
Control Type	Toggle
Breaking Capacity Code	J
Breaking Capacity	100 kA 240 V AC 50/60 Hz UL 489 65 kA 480 V AC 50/60 Hz UL 489 25 kA 600 V AC 50/60 Hz UL 489 20 kA 250 V DC UL 489
[Ue] Rated Operational Voltage	600 V AC 50/60 Hz IEC 60947-3
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	65 kA 220/240 V AC 50/60 Hz IEC 60947-2 35 kA 380/440/415 V AC 50/60 Hz IEC 60947-2 18 kA 500/525 V AC 50/60 Hz IEC 60947-2 20 kA 250 V DC IEC 60947-2 20 kA 500 V DC IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Trip Unit Technology	Thermal-magnetic
Magnetic Tripping Current	1750 A
Magnetic Hold Current	875 A
Continuous Current Rating	80 %
[Ui] Rated Insulation Voltage	750 V IEC 60947-2
Protection Type	Overload protection Short-circuit protection
Accessory / Separate Part Type	Auxiliary switch 24 V AC/DC 1 NO + 1 NC cover frame
Suitability For Isolation	Yes IEC 60947-2
Utilisation Category	Category A
Awg Gauge	AWG 4AWG 4/0 aluminium/copper terminal

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Local Signalling	Switched off (OFF) 1 trip indicator green)	
Mounting Mode	Unit mount lug)	
Mounting Support	Lug	
Electrical Connection	Lugs, line Lugs, load	
Terminal Identifier	AL175JD	
Long Time Pick-Up Adjustment Range	0.251 x ln	
Mounting Height	4.5 in (114.30 mm)	
Tightening Torque	221.27 lbf.in (25 N.m) 0.040.15 in <sup>2</sup> (2595 mm <sup>2</sup> ) (AWG 4AWG 4/0)	
Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in)	
Power Wire Stripping Length	0.98 in (25 mm)	
Height	7.52 in (191 mm)	
Width	4.09 in (104 mm)	
Depth	3.39 in (86 mm)	
Net Weight	5.29 lb(US) (2.4 kg)	
Phase Connection	ABC	
Communication Interface	Modbus Ethernet	
Circuit Breaker Application	HACR rated	

### Environment

Quality Labels	CE
Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2
Product Certifications	UL CSA NOM
Ip Degree Of Protection	Front cover IP40
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	28158 °F (-270 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	< 6561.68 ft (2000 m) without derating 5000 m with derating

# Ordering and shipping details

Category	US10DE201115	
Discount Schedule	0DE2	
Returnability	No	
Country Of Origin	US	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.13 in (13.018 cm)
Package 1 Width	7.25 in (18.415 cm)
Package 1 Length	8.44 in (21.433 cm)
Package 1 Weight	5.00 lb(US) (2.268 kg)

### **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov