Product data sheet

Specifications





Circuit breaker

Circuit breaker, PowerPacT J, 175A, 3 pole, 500VDC, 50kA, lugs, thermal magnetic, 80%

JLL37175D81

Main

Product Or Component Type

Complementary

Line Rated Current	175 A
Number Of Poles	3P
Control Type	Toggle
Breaking Capacity Code	L
Breaking Capacity	125 kA 240 V AC 50/60 Hz UL 489
	100 kA 480 V AC 50/60 Hz UL 489
	50 kA 600 V AC 50/60 Hz UL 489
	20 kA 250 V DC UL 489
	50 kA 500 V DC UL 489
Ue] Rated Operational Voltage	500 V DC IEC 60947-3
[Ics] Rated Service Breaking	125 kA 220/240 V AC 50/60 Hz IEC 60947-2
Capacity	100 kA 380/440/415 V AC 50/60 Hz IEC 60947-2
	50 kA 500/525 V AC 50/60 Hz IEC 60947-2
	20 kA 250 V DC IEC 60947-2
	20 kA 500 V DC IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Trip Unit Technology	Thermal-magnetic
Magnetic Tripping Current	350600 A
Continuous Current Rating	80 %
[Ui] Rated Insulation Voltage	750 V IEC 60947-2
Protection Type	Overload protection
	Short-circuit protection
Suitability For Isolation	Yes IEC 60947-2
Utilisation Category	Category A
Awg Gauge	AWG 4AWG 4/0 aluminium/copper terminal
Local Signalling	Switched off (OFF) 1 trip indicator green)
Mounting Mode	Unit mount lug)
Mounting Support	Lug
	Luy
Electrical Connection	Lugs, line
	Lugs, load
Terminal Identifier	AL175JD
Long Time Pick-Up Adjustment Range	0.251 x ln

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in)
Power Wire Stripping Length	0.98 in (25 mm)
Height	7.52 in (191 mm)
Width	4.09 in (104 mm)
Depth	3.39 in (86 mm)
Net Weight	5.29 lb(US) (2.4 kg)
Communication Interface	Modbus
Circuit Breaker Application	HACR rated

Environment

Quality Labels	CE
Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2
Product Certifications	UL CSA NOM
Ip Degree Of Protection	Front cover IP40
Pollution Degree	3
Ambient Air Temperature For Operation	28158 °F (-270 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	< 6561.68 ft (2000 m) without derating 5000 m with derating

Ordering and shipping details

Category	01120-HL,JL UNIT MT BREAKER/SWITCH
Discount Schedule	DE2
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	8.29 lb(US) (3.76 kg)

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov