Product data sheet

Specifications





! Discontinued - Service only

Advanced touchscreen panel, Harmony GTO, 10.4 Color Touch VGA Stainless, logo removed

HMIGTO5315FW

- ! Discontinued on: Jun 30, 2023
- ! To be end-of-service on: Mar 31, 2027

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony GTO	
Product Or Component Type	Advanced touchscreen panel	
Display Colour	65536 colours	
Display Size	10.4 inch	
Supply	External source	
Battery Type	Lithium internal RAM 100 days 5 day(s) 10 year(s)	
Provided Equipment	1 protective cover	

Complementary

Terminal Type	Touchscreen display
Display Type	Backlit colour TFT LCD
Display Resolution	640 x 480 pixels VGA
Touch Sensitive Zone	1024 x 1024
Touch Panel	Resistive film, 1000000 cycles
Backlight Lifespan	50000 hours white 77 °F (25 °C)
Brightness	16 levels by touch panel 16 levels by software
Character Font	ASCII Chinese (simplified Chinese) Japanese (ANK, Kanji) Taiwanese (traditional Chinese) Korean
[Us] Rated Supply Voltage	24 V DC
Supply Voltage Limits	19.228.8 V
Inrush Current	30 A
Maximum Power Consumption In W	12 W when power is not supplied to external devices 7 W when backlight is OFF 8 W when backlight is dimmed

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

17 W

Local Cianallina	
Local Signalling	Status LED green, steady offline
g	Status LED green, steady operating
	Status LED orange, flashing software starting up
	Status LED red, steady power supply (ON)
	Status LED clear, faded power supply (OFF)
	COM2 LED yellow, steady data is being transmitted
	COM2 LED yellow, faded no data transmission
	SD card LED green, steady card is inserted SD card LED green, faded card is not inserted or is not being accessed
	3D card LED green, laded card is not inserted or is not being accessed
Software Designation	Vijeo Designer configuration software >= V6.1
Memory Description	Flash EPROM, 96 MB
Data Backed Up	512 KB internal RAM SRAM)
Data Storage Equipment	SD card, <= 32 GB SDHC card, <= 32 GB
Downloadable Protocols	Schneider Electric Modicon Modbus
	Schneider Electric Modicon Uni-TE
	Schneider Electric Modicon Modbus Plus
	Schneider Electric Modicon FIPWAY
	Mitsubishi Melsec third party protocols Omron Sysmac third party protocols
	Rockwell Automation Allen-Bradley third party protocols
	Siemens Simatic third party protocols
	Schneider Electric Modicon Modbus TCP
Integrated Connection Type	COM1 serial link SUB-D 9 RS232C 2400115200 bps
	COM2 serial link RJ45 RS485 2400115200 bps
	COM2 serial link RJ45 RS485 187.5 kbps Siemens MPI
	Ethernet RJ45 10BASE-T/100BASE-TX
	Ethernet RJ45 IEEE 802.3
	USB 2.0 type A
	USB 2.0 type mini B
Product Mounting	Flush mounting
Fixing Mode	by 8 nuts by 4 L brackets
Front Material	Stainless steel 304
Enclosure Material	PPT
Type Of Cooling	Natural convection
	12.46 in (316.5 mm)
Width	12. 10 III (0 10.0 11IIII)
Width Height	10.18 in (258.5 mm)
Height	10.18 in (258.5 mm)
Height Depth	10.18 in (258.5 mm) 2.24 in (57 mm)
Height Depth Net Weight	10.18 in (258.5 mm) 2.24 in (57 mm)
Depth Net Weight Environment	10.18 in (258.5 mm) 2.24 in (57 mm) 5.51 lb(US) (2.5 kg)
Height Depth Net Weight Environment	10.18 in (258.5 mm) 2.24 in (57 mm) 5.51 lb(US) (2.5 kg) EN 61131-2
Height Depth Net Weight Environment	10.18 in (258.5 mm) 2.24 in (57 mm) 5.51 lb(US) (2.5 kg) EN 61131-2 UL 508
Height Depth Net Weight Environment Standards	10.18 in (258.5 mm) 2.24 in (57 mm) 5.51 lb(US) (2.5 kg) EN 61131-2 UL 508 IEC 61000-6-2
Height Depth Net Weight Environment Standards	10.18 in (258.5 mm) 2.24 in (57 mm) 5.51 lb(US) (2.5 kg) EN 61131-2 UL 508 IEC 61000-6-2 CE
Height Depth Net Weight Environment Standards	10.18 in (258.5 mm) 2.24 in (57 mm) 5.51 lb(US) (2.5 kg) EN 61131-2 UL 508 IEC 61000-6-2 CE KCC C-tick cULus
Height Depth Net Weight Environment Standards	10.18 in (258.5 mm) 2.24 in (57 mm) 5.51 lb(US) (2.5 kg) EN 61131-2 UL 508 IEC 61000-6-2 CE KCC C-tick cULus UKCA
Height Depth Net Weight Environment Standards	10.18 in (258.5 mm) 2.24 in (57 mm) 5.51 lb(US) (2.5 kg) EN 61131-2 UL 508 IEC 61000-6-2 CE KCC C-tick cULus
Height Depth Net Weight Environment Standards	10.18 in (258.5 mm) 2.24 in (57 mm) 5.51 lb(US) (2.5 kg) EN 61131-2 UL 508 IEC 61000-6-2 CE KCC C-tick cULus UKCA
Height Depth Net Weight Environment Standards Product Certifications Ambient Air Temperature For	10.18 in (258.5 mm) 2.24 in (57 mm) 5.51 lb(US) (2.5 kg) EN 61131-2 UL 508 IEC 61000-6-2 CE KCC C-tick cULus UKCA UKEX
Height Depth Net Weight Environment Standards Product Certifications Ambient Air Temperature For Operation Ambient Air Temperature For	10.18 in (258.5 mm) 2.24 in (57 mm) 5.51 lb(US) (2.5 kg) EN 61131-2 UL 508 IEC 61000-6-2 CE KCC C-tick cULus UKCA UKEX 32131 °F (055 °C)

Ip Degree Of Protection	IP20 IEC 60529 rear panel) IP65 IEC 60529 front panel)	
Nema Degree Of Protection	NEMA 4X front panel (indoor use)	
Shock Resistance	147 m/s ² 3 chocks in each direction X, Y and Z EN/IEC 61131-2	
Vibration Resistance	3.5 mm 59 Hz) - X, Y, Z directions for 10 cycles (approx. 100 min) - EN/IEC 61131-2 1 gn 9150 Hz) - X, Y, Z directions for 10 cycles (approx. 100 min) - EN/IEC 61131-2	
Resistance To Electrostatic Discharge	6 kV contact discharge IEC 61000-4-2 level 3	

Ordering and shipping details

Category	US10MC222569
Discount Schedule	0MC2
Gtin	3606480841736
Returnability	No
Country Of Origin	SG

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	7.09 in (18.0 cm)	
Package 1 Width	12.99 in (33.0 cm)	
Package 1 Length	15.75 in (40.0 cm)	
Package 1 Weight	7.68 lb(US) (3.482 kg)	
Unit Type Of Package 2	CAR	
Number Of Units In Package 2	2	
Package 2 Height	16.93 in (43.0 cm)	
Package 2 Width	13.98 in (35.5 cm)	
Package 2 Length	17.91 in (45.5 cm)	
Package 2 Weight	15.35 lb(US) (6.964 kg)	

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov