# Product data sheet

Specifications





(!) Discontinued - Service only

### Advanced touchscreen panel, Harmony GTO, 12.1 Color Touch SVGA Stainless, logo removed

HMIGTO6315FW

! Discontinued on: Jun 30, 2023

① To be end-of-service on: Mar 31, 2027

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range Of Product	Harmony GTO	
Product Or Component Type	Advanced touchscreen panel	
Display Colour	65536 colours	
Display Size	12.1 inch	
Supply	External source	
Battery Type	Lithium internal RAM 100 days 5 day(s) 10 year(s)	
Provided Equipment	1 protective cover	

#### Complementary

Terminal Type	Touchscreen display
Display Type	Backlit colour TFT LCD
Display Resolution	800 x 600 pixels SVGA
Touch Sensitive Zone	1024 x 1024
Touch Panel	Resistive film, 1000000 cycles
Backlight Lifespan	50000 hours white 77 °F (25 °C)
Brightness	16 levels by touch panel 16 levels by software
Character Font	Japanese (ANK, Kanji) Taiwanese (traditional Chinese) Chinese (simplified Chinese) Korean ASCII (European characters)
[Us] Rated Supply Voltage	24 V DC
Supply Voltage Limits	19.228.8 V
Inrush Current	30 A
Maximum Power Consumption In W	12 W when power is not supplied to external devices 7 W when backlight is OFF 8 W when backlight is dimmed

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

17 W

Local Signalling	Status LED green, steady offline
	Status LED green, steady operating
	Status LED orange, flashing software starting up
	Status LED red, steady power supply (ON)
	Status LED clear, faded power supply (OFF)
	COM2 LED yellow, steady data is being transmitted
	COM2 LED yellow, faded no data transmission
	SD card LED green, steady card is inserted SD card LED green, faded card is not inserted or is not being accessed
	SD card LED green, raded card is not inserted or is not being accessed
Software Designation	Vijeo Designer configuration software >= V6.1
Memory Description	Flash EPROM, 96 MB
Data Backed Up	512 KB internal RAM SRAM)
Data Storage Equipment	SD card, <= 32 GB SDHC card, <= 32 GB
Downloadable Protocols	Schneider Electric Modicon Modbus
	Schneider Electric Modicon Uni-TE
	Schneider Electric Modicon Modbus Plus
	Schneider Electric Modicon FIPWAY
	Mitsubishi Melsec third party protocols
	Omron Sysmac third party protocols  Rockwell Automation Allen-Bradley third party protocols
	Rockwell Automation Allen-Bradley third party protocols Siemens Simatic third party protocols
	Schneider Electric Modicon Modbus TCP
Integrated Connection Type	COM1 serial link SUB-D 9 RS232C 2400115200 bps
	COM1 serial link S0B-D 9 RS232C 2400115200 bps COM2 serial link RJ45 RS485 2400115200 bps
	COM2 serial link RJ45 RS485 187.5 kbps Siemens MPI
	Ethernet RJ45 10BASE-T/100BASE-TX
	Ethernet RJ45 IEEE 802.3
	USB 2.0 type A
	USB 2.0 type mini B
Product Mounting	Flush mounting
Fixing Mode	by 8 nuts
	by 4 L brackets
Front Material	Stainless steel 304
Enclosure Material	РРТ
Type Of Cooling	Natural convection
Width	14.13 in (359 mm)
Height	11.22 in (285 mm)
Depth	2.20 in (56 mm)
Net Weight	6.61 lb(US) (3 kg)
Environment	
Environment Standards	EN 61131-2
	EN 61131-2 UL 508
	UL 508
Standards	UL 508 IEC 61000-6-2
Standards	UL 508 IEC 61000-6-2 cULus
Standards	UL 508 IEC 61000-6-2 cULus C-tick
Standards	UL 508 IEC 61000-6-2  cULus C-tick CE KCC UKCA
Standards	UL 508 IEC 61000-6-2 cULus C-tick CE KCC
Standards	UL 508 IEC 61000-6-2  cULus C-tick CE KCC UKCA
Standards  Product Certifications  Ambient Air Temperature For	UL 508 IEC 61000-6-2  cULus C-tick CE KCC UKCA UKEX
Product Certifications  Ambient Air Temperature For Operation  Ambient Air Temperature For	UL 508 IEC 61000-6-2 cULus C-tick CE KCC UKCA UKEX 32131 °F (055 °C)

Ip Degree Of Protection	IP20 IEC 60529 rear panel) IP65 IEC 60529 front panel)	
Nema Degree Of Protection	NEMA 4X front panel (indoor use)	
Shock Resistance	147 m/s² 3 chocks in each direction X, Y and Z EN/IEC 61131-2	
Vibration Resistance	3.5 mm 59 Hz) - X, Y, Z directions for 10 cycles (approx. 100 min) - EN/IEC 61131-2 1 gn 9150 Hz) - X, Y, Z directions for 10 cycles (approx. 100 min) - EN/IEC 61131-2	
Resistance To Electrostatic Discharge	6 kV contact discharge IEC 61000-4-2 level 3	

### Ordering and shipping details

Category	US10MC222569
Discount Schedule	0MC2
Gtin	3606480841712
Returnability	No
Country Of Origin	CN

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.27 in (21.0 cm)
Package 1 Width	16.54 in (42.0 cm)
Package 1 Length	21.26 in (54.0 cm)
Package 1 Weight	10.60 lb(US) (4.806 kg)

### Sustainability Screen Premium

Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov