

Hanger, I-Line Busway, max 600A rated, vertical installation, aluminum

HP4V

! Discontinued on: Jun 30, 2023

! Discontinued

Main

Product	Hanger
Range	I-I ine

Complementary

Rated Current	600 A aluminium
Orientation	Vertical

Environment

Standards	UL 857	
	CSA C22.2 No 27:1994	
	IEC 61439-6	

Ordering and shipping details

Category	20204-HANGERS WITH BILLING	
Discount Schedule	PE8	
Gtin	785901506362	
Returnability	No	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	5.30 lb(US) (2.404 kg)

Contractual warranty

	<u> </u>
·	
Warranty	18 months

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information Yes	
Ø	Pvc Free	

Certifications & Standards

Reach Regulation

Nedon Negaliation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov