

# Product data sheet

Specifications

SQUARE D



Switchgear, HVL switch, 600A, 4.76 kV, 3 pole, switch mechanism, NEMA 1

HVL305NG

Product availability: Stock - Normally stocked in distribution facility

Price\*: 17,500.00 USD

## Main

Product	Switch mechanism
---------	------------------

## Complementary

Line Rated Current	600 A
Momentary Amperes Asymmetrical	40 kA
Frequency	50/60 Hz
Number Of Poles	3P
Highest Voltage For Equipment (Um)	4.76 kV
Basic Inulation Level	60 kV
Enclosure Rating	NEMA 1
Electrical Connection	Lugs
Type Of Installation	Indoor
Wire Gauge	AWG 2...600 kcmil aluminium/copper
Enclosure Width	38 in (965.20 mm)
Enclosure Depth	54.5 in (1384.30 mm)
Enclosure Height	90 in (2286.00 mm)

## Environment

Product Certifications	UL Listed cUL
------------------------	------------------

## Ordering and shipping details

Category	07942-5KV DIGEST HVL NEMA 1
Discount Schedule	PE5A
Returnability	Yes
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	1200.00 lb(US) (544.311 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation

---