

Product data sheet

Specifications



Switchgear, HVL, single, 600A, 17kV, 3 pole, 10E to 400E boric acid fuse, NEMA 3R

HVL317BW

Product availability: Stock - Normally stocked in distribution facility

Price*: 34,098.00 USD

Main

Product	Switched fuse mechanism
Included Accessory	Enclosure heater
Not Included	fuse to be ordered separately

Complementary

Protection Type	Fuse boric acid
Associated Fuse Rating	10 A E 15 A E 20 A E 25 A E 30 A E 40 A E 50 A E 65 A E 80 A E 100 A E 125 A E 150 A E 175 A E 200 A E 250 A E 300 A E 400 A E
Line Rated Current	600 A
Momentary Amperes Asymmetrical	61 kA
Frequency	50/60 Hz
Number Of Poles	3P
Highest Voltage For Equipment (Um)	17 kV
Basic Inulation Level	95 kV
Enclosure Rating	NEMA 3R
Electrical Connection	Lugs
Type Of Installation	Outdoor
Wire Gauge	AWG 2...600 kcmil aluminium/copper
Enclosure Width	38 in (965.20 mm)
Enclosure Depth	60 in (1524.00 mm)
Enclosure Height	97 in (2463.80 mm)

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	UL Listed cUL
------------------------	------------------

Ordering and shipping details

Category	07945-15KV DIGEST HVL NEMA 3R
Discount Schedule	PE5A
Gtin	3606486276433
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	1400.00 lb(US) (635.029 kg)

Contractual warranty

Warranty	18 months
----------	-----------