Specifications





K1D504H

() Discontinued on: Jan 18, 2021

A - rear mounting

body for switch - 4-pole - 90° - 12



Main

Range Of Product	Harmony K	
Product Or Component Type	Cam switch body	
Component Name	K1	
[Ith] Conventional Free Air Thermal Current	12 A	
Sub-Assembly Composition	Contact blocks + fixing plate	
Cam Switch Function	Switch	
Off Position	With Off position	
Poles Description	4P	
Switching Positions	Right: 0° - 90°	
Mounting Location	Rear	
Fixing Mode	4 holes	
Bezel Material	Plastic	

Complementary

Switching Angle	90 °	
[Ui] Rated Insulation Voltage	690 V 3)IEC 60947-1	
[Ithe] Conventional Enclosed Thermal Current	10 A	
Rated Operational Power In W	10500 W AC-21, 500 - 660 V 3 phase IEC 947-3 1100 W AC-3, 230 V 3 phase IEC 947-3 1500 W AC-3, 230 V 3 phase IEC 947-3 1500 W AC-3, 400 V 1 phase IEC 947-3 1500 W AC-3, 400 V 3 phase IEC 947-3 1500 W AC-3, 500 V 3 phase IEC 947-3 2200 W AC-23A, 400 V 3 phase IEC 947-3 2200 W AC-23A, 500 V 3 phase IEC 947-3 2200 W AC-23A, 690 V 3 phase IEC 947-3 2200 W AC-23A, 690 V 3 phase IEC 947-3 600 W AC-3, 230 V 1 phase IEC 947-3 8300 W AC-21, 400 V 3 phase IEC 947-3	
[le] Rated Operational Current Ac	1.8 A 690 V AC-3 3 phase IEC 947-3 2.8 A 500 V AC-3 3 phase IEC 947-3 2.8 A 690 V AC-23A 3 phase IEC 947-3 3.3 A 400 V AC-3 3 phase IEC 947-3 3.8 A 500 V AC-23A 3 phase IEC 947-3 4.6 A 230 V AC-3 3 phase IEC 947-3 4.8 A 400 V AC-23A 3 phase IEC 947-3 5.6 A 230 V AC-23A 3 phase IEC 947-3 1 A 500 V AC-15 IEC 947-5-1 2 A 400 V AC-15 IEC 947-5-1 3 A 230 V AC-15 IEC 947-5-1	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

1000000 cycles AC-15	
1000000 cycles AC-21	
500000 cycles AC-23	
500000 cycles AC-3	
2.5 cyc/mn AC-21	
2.5 cyc/mn AC-23	
2.5 cyc/mn AC-3	
8.333 cyc/mn AC-15	
10000 A	
16 A cartridge fuse gG	
4 kV in isolating function 6 kV IEC 947-1	
Slow-break	
With	
Captive screw clamp terminals flexible 2 x 1.5 mm ²	
Captive screw clamp terminals solid 1 x 2.5 mm ²	
1000000 cycles	
0.33 lb(US) (0.15 kg)	

Environment

Standards	EN 60947-3 power circuit EN 60947-5-1 control circuit CENELEC EN 50013	
Product Certifications	CSA 240 V 3 hp 3 phase 2 UL 240 V 0.33 hp 1 phase 2 CSA 240 V 1 hp 1 phase UL 240 V 1 hp 3 phase	
Protective Treatment	TC	
Ambient Air Temperature For Operation	-13131 °F (-2555 °C)	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Shock Resistance	30 gn IEC 68-2-27	
Vibration Resistance	5 gn 10150 Hz)IEC 68-2-6	
Overvoltage Category	Class II IEC 536 Class II NF C 20-030	

Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)	
Discount Schedule	CS2	
Gtin	3389110445992	
Returnability	No	

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	No need of specific recycling operations	
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

Dimensions Drawings

Body

Rear Mounting




a4 52.5 mm/2.07 in.

(1) Panel cut-out: Ø 10 mm/0.39 in. central hole

Technical Description

Link Positions (Factory Mounted)



Angular Position of Switch



Switching Program

0	90	
	\bigtriangledown	1
	\wedge	2
	\checkmark	3
	\wedge	4
	\checkmark	5
	\wedge	6
	\checkmark	7
	\land	8

Convention Used for Switching Program Representation

Contact closed Contact closed in 2 positions and maintained between the 2 positions Sealed assembly for auto-maintain control Overlapping contacts

Spring return position: for a switching angle of 90°, spring return is over 30° after the last position (for a maximum of 3 simultaneous contacts).

Example:

