





Circuit breaker, PowerPacT J, 250A, 3 pole, 480VAC, 100kA, lugs, Micrologic 3.2, 80%, mission critical

JLL34250WU31X

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 8,629.00 USD

Complementary

Line Rated Current	250 A	
Number Of Poles	3P	
Control Type	Toggle	
Breaking Capacity Code	L	
Breaking Capacity	125 kA 240 V AC 50/60 Hz UL 489 100 kA 480 V AC 50/60 Hz UL 489 50 kA 600 V AC 50/60 Hz UL 489 20 kA 250 V DC UL 489 50 kA 500 V DC UL 489	
[Ue] Rated Operational Voltage	480/277 V AC 50/60 Hz	
Network Frequency	50/60 Hz	
[lcs] Rated Service Breaking Capacity	125 kA 220/240 V AC 50/60 Hz IEC 60947-2 100 kA 380/440/415 V AC 50/60 Hz IEC 60947-2 50 kA 500/525 V AC 50/60 Hz IEC 60947-2 20 kA 250 V DC IEC 60947-2 20 kA 500 V DC IEC 60947-2	
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2	
Trip Unit Technology	Electronic, standard, MicroLogic 3.2, LI	
Continuous Current Rating	80 %	
[Ui] Rated Insulation Voltage	750 V IEC 60947-2	
Trip Unit Name	MicroLogic 3.2	
Protection Type	Overload protection Short-circuit protection	
Suitability For Isolation	Yes IEC 60947-2	
Utilisation Category	Category A	
Awg Gauge	AWG 3/0350 kcmil aluminium/copper terminals	
Local Signalling	Ready 1 LED green) Alarm 1 LED 90 % Ir orange) Alarm 1 LED 105 % Ir red) Switched off (OFF) 1 trip indicator green)	
Mounting Mode	Unit mount lug)	
Mounting Support	Lug	
Electrical Connection	Lugs, line Lugs, load	
Terminal Identifier	AL250JD	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Long Time Pick-Up Adjustment Range	0.251 x ln
Tightening Torque	221.27 lbf.in (25 N.m) 0.150.29 in² (95185 mm²) (AWG 3/0350 kcmil)
Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in)
Power Wire Stripping Length	0.98 in (25 mm)
Height	7.52 in (191 mm)
Width	4.09 in (104 mm)
Depth	3.39 in (86 mm)
Net Weight	5.29 lb(US) (2.4 kg)
Communication Interface	Modbus

Environment

Quality Labels	CE	
Standards	UL	
	CSA	
	NEMA	
	NOM-003-SCFI-2000	
	IEC 60947-2	
Product Certifications	UL	
	CSA	
	NOM	
Ip Degree Of Protection	Front cover IP40	
Pollution Degree	3	
Ambient Air Temperature For Operation	28158 °F (-270 °C)	
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)	
Operating Altitude	< 6561.68 ft (2000 m) without derating 5000 m with derating	

Ordering and shipping details

Category	US10DE201107
Discount Schedule	0DE2
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.13 in (13.018 cm)
Package 1 Width	7.25 in (18.415 cm)
Package 1 Length	8.44 in (21.433 cm)
Package 1 Weight	5.00 lb(US) (2.268 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov