

Product data sheet

Specifications



TeSys Deca - protective cover - for LC1 D115...D150

LAD9ET4

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 6.24 USD

Main

Range Of Product	TeSys Deca
Range	TeSys
Device Short Name	LAD9
Product Or Component Type	Protective cover
Accessory / Separate Part Category	Installation accessory
Product Compatibility	LC1D115 LC1D150

Complementary

Net Weight	0.14 oz (4 g)
------------	---------------

Ordering and shipping details

Category	US10I1222341
Discount Schedule	0I12
Gtin	3389110948790
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.36 in (6 cm)
Package 1 Width	6.22 in (15.8 cm)
Package 1 Length	4.41 in (11.2 cm)
Package 1 Weight	1.90 oz (54 g)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)