Product data sheet

Specifications





body for switch - 6-pole - 12 A

K1F026X

() Discontinued on: Jan 29, 2021



Main

Range Of Product	Harmony K
Product Or Component Type	Complete cam switch
Component Name	К1
[Ith] Conventional Free Air Thermal Current	12 A
Sub-Assembly Composition	Contact blocks + fixing plate
Cam Switch Function	Switch
Off Position	With Off position
Poles Description	6P
Switching Positions	Right: 0° - 90°
Mounting Location	Front
Fixing Mode	Ø 22 mm hole
Bezel Material	Plastic

Complementary

Switching Angle	45 °
[Ui] Rated Insulation Voltage	690 V 3)IEC 60947-1
[Ithe] Conventional Enclosed Thermal Current	10 A
Rated Operational Power In W	10500 W AC-21, 500 - 660 V 3 phase IEC 947-3
[Ie] Rated Operational Current Ac	1 A 500 V AC-15 IEC 947-5-1
Electrical Durability	1000000 cycles AC-15
Maximum Operating Rate	2.5 cyc/mn AC-21
Short-Circuit Current	10000 A
Short-Circuit Protection	20 A cartridge fuse gG
[Uimp] Rated Impulse Withstand Voltage	4 kV in isolating function
Contact Operation	Slow-break
Positive Opening	With
Electrical Connection	Captive screw clamp terminals flexible 2 x 1.5 mm ²
Mechanical Durability	1000000 cycles

1000000 cycles

Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Standards	CENELEC EN 50013
Product Certifications	CSA 240 V 1 hp 1 phase
Protective Treatment	TC
Ambient Air Temperature For Operation	-13131 °F (-2555 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Shock Resistance	30 gn IEC 68-2-27
Vibration Resistance	5 gn 10150 Hz)IEC 68-2-6
Overvoltage Category	Class II IEC 536
Ip Degree Of Protection	IP40 conforming to IEC 529

Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)
Discount Schedule	CS2
Gtin	3389110475319
Returnability	No

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov