Product data sheet





IEC contactor, TeSys Deca, nonreversing, 60A resistive, 4 pole, 4 NO, 400VAC 50/60Hz coil, open style

LC1DT60AV7

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 353.16 USD

Main	
Range	TeSys TeSys Deca
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load
Utilisation Category	AC-1
Poles Description	4P
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC
[le] Rated Operational Current	60 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit
[Uc] Control Circuit Voltage	400 V AC 50/60 Hz
Complementary	
Compatibility Code	LC1D
Pole Contact Composition	4 NO

Compatibility Code	LC1D
Pole Contact Composition	4 NO
Protective Cover	With
[Ith] Conventional Free Air Thermal Current	10 A (at 140 °F (60 °C)) for signalling circuit 60 A (at 140 °F (60 °C)) for power circuit
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 800 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	800 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	320 A 104 °F (40 °C) - 10 s for power circuit 720 A 104 °F (40 °C) - 1 s for power circuit 72 A 104 °F (40 °C) - 10 min for power circuit 165 A 104 °F (40 °C) - 1 min for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 80 A gG at <= 690 V coordination type 1 for power circuit 80 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	1.6 mOhm - Ith 60 A 50 Hz for power circuit
Power Dissipation Per Pole	5.8 W AC-1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

[Ui] Rated Insulation Voltage	Power circuit 600 V CSA Power circuit 600 V UL Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL Power circuit 690 V IEC 60947-4-1
Overvoltage Category	Ш
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	6 Mcycles
Electrical Durability	1.4 Mcycles 60 A AC-1 <= 440 V
Control Circuit Type	AC 50/60 Hz
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc -40158 °F (-4070 °C) drop-out AC 50/60 Hz 0.81.1 Uc -40140 °F (-4060 °C) operational AC 50 Hz 0.851.1 Uc -40140 °F (-4060 °C) operational AC 60 Hz 11.1 Uc 140158 °F (6070 °C) operational AC 50/60 Hz
Inrush Power In Va	140 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C)) 160 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	13 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C)) 15 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat Dissipation	45 W at 50/60 Hz
Operating Time	419 ms opening 1226 ms closing
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)
Connections - Terminals	Control circuit: screw clamp terminals 2 0.000.00 in² (12.5 mm²) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end Power circuit: screw clamp terminal 1 0.000.05 in² (135 mm²) - cable stiffness: flexible without cable end Power circuit: screw clamp terminal 2 0.000.04 in² (125 mm²) - cable stiffness: flexible with cable end Power circuit: screw clamp terminal 2 0.000.05 in² (135 mm²) - cable stiffness: flexible with cable end Power circuit: screw clamp terminal 2 0.000.05 in² (135 mm²) - cable stiffness: flexible with cable end Power circuit: screw clamp terminal 2 0.000.05 in² (135 mm²) - cable stiffness: solid without cable end Power circuit: screw clamp terminal 1 0.000.05 in² (135 mm²) - cable stiffness: solid without cable end Power circuit: screw clamp terminal 2 0.000.05 in² (135 mm²) - cable stiffness: solid without cable end
Tightening Torque Auxiliary Contact Composition	Control circuit 15.05 lbf.in (1.7 N.m) EverLink BTR screw connectors flat Ø 6 mm Control circuit 15.05 lbf.in (1.7 N.m) EverLink BTR screw connectors Philips No 2 Power circuit 70.81 lbf.in (8 N.m) EverLink BTR screw connectors 0.040.05 in² (2535 mm²) hexagonal 0.16 in (4 mm) Power circuit 44.25 lbf.in (5 N.m) EverLink BTR screw connectors 0.000.04 in² (1 25 mm²) hexagonal 0.16 in (4 mm) Control circuit 15.05 lbf.in (1.7 N.m) EverLink BTR screw connectors pozidriv No 2 Power circuit 22.13 lbf.in (2.5 N.m) EverLink BTR screw connectors pozidriv No 2

Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1	
	WIITO CORRECT INC IEC 00347-4-1	
Signalling Circuit Frequency	25400 Hz	
Minimum Switching Voltage	17 V for signalling circuit	
Minimum Switching Current	5 mA for signalling circuit	
Insulation Resistance	> 10 MOhm for signalling circuit	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact	
	1.5 ms on energisation between NC and NO contact	
Mounting Support	Plate	
	Rail	

Environment

Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1
	IEC 60947-4-1
	IEC 60947-5-1
	UL 508
	IEC 60335-1
Product Certifications	RINA
	GL
	DNV
	CSA
	CCC
	BV
	UL
	LROS (Lloyds register of shipping)
	GOST
Ip Degree Of Protection	IP20 front face IEC 60529
Protective Treatment	THIEC 60068-2-30
Climatic Withstand	IACS E10 exposure to damp heat
	IEC 60947-1 Annex Q category D exposure to damp heat
	12.0 00347-1 741110X & category D exposure to damp fleat
Permissible Ambient Air	-40140 °F (-4060 °C)
Temperature Around The Device	140158 °F (6070 °C) with derating
Operating Altitude	09842.52 ft (03000 m)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
	V F GOTHOLIMING TO GE G F
Mechanical Robustness	Vibrations contactor open 2 Gn, 5300 Hz)
	Vibrations contactor closed 4 Gn, 5300 Hz)
	Shocks contactor closed 15 Gn for 11 ms)
	Shocks contactor open 10 Gn for 11 ms)
	- Choose contactor open to cities thine,
Height	4.80 in (122 mm)
Width	2.76 in (70 mm)
Depth	4.72 in (120 mm)
Net Weight	2.40 lb(US) (1.09 kg)

Ordering and shipping details

Category	US10I1222357
Discount Schedule	0112
Gtin	3389119409339
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.11 in (7.9 cm)
Package 1 Width	5.43 in (13.8 cm)
Package 1 Length	6.02 in (15.3 cm)
Package 1 Weight	2.39 lb(US) (1.085 kg)
Unit Type Of Package 2	S02
Number Of Units In Package 2	7
Package 2 Height	5.91 in (15 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	17.73 lb(US) (8.043 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	112
Package 3 Height	30.31 in (77 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	301.95 lb(US) (136.964 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
②	Toxic Heavy Metal Free
⊘	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov