# Product data sheet





## TeSys D thermal overload relays remote electrical tripping - 48 V DC/AC

LA7D03E

! Discontinued on: Oct 8, 2021

(!) Discontinued

#### Main

Range	TeSys	
Product Or Component Type	Electrical remote tripping	
Device Short Name	LA7D	
Accessory / Separate Part Category	Electrical accessory	
Product Compatibility	LR3D35 LRD43 LRD33 LR3D43 LRD15 LRD15 LR2D LR3D15 LR3D33	
[Uc] Control Circuit Voltage	48 V AC 50/60 Hz 48 V DC	

### Complementary

Maximum Inrush Power In Va	100 VA
Inrush Power In W	0100 W
Net Weight	0.20 lb(US) (0.09 kg)

## Ordering and shipping details

Category	18402-WORLD SERVICE PARTS(CONTROL ACCESS)	
Discount Schedule	CP10	
Gtin	3389110055115	
Returnability	No	
Country Of Origin	FR	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5 cm)
Package 1 Width	1.89 in (4.8 cm)
Package 1 Length	1.89 in (4.8 cm)
Package 1 Weight	3.70 oz (105 g)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

## **Contractual warranty**

Warranty

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.