Product data sheet

Specifications





Auxiliary contact block, TeSys Deca, 2NC, front mounting, spring terminals

LADN023

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 27.24 USD

Main

Range	TeSys TeSys Deca	
Product Name	TeSys Deca	
Product Or Component Type	Auxiliary contact block	
Device Short Name	LADN	
Range Compatibility	TeSys Deca CAD TeSys Deca LC1D	
Mounting Location	Front	
Pole Contact Composition	2 NC	
Contacts Operation	Instantaneous	
[Ue] Rated Operational Voltage	690 V AC 25400 Hz	
[Ie] Rated Operational Current	6 A at 120 V AC-15 1.04 A at 690 V AC-15 0.55 A at 125 V DC-13 0.1 A at 600 V DC-13	
[Ui] Rated Insulation Voltage	690 V IEC 60947-5-1 600 V UL 60947-5-1 600 V CSA C22.2 No 60947-5-1	
[Ith] Conventional Free Air Thermal Current	10 A (at 140 °F (60 °C))	
Standards	EN/IEC 60947-5-1 UL 60947-5-1 CSA C22.2 No 60947-5-1 GB/T 14048.5	
Product Certifications	IECEE CB Scheme UL CSA CCC EAC UKCA	

Complementary

Irms Rated Making Capacity	140 A AC conforming to IEC 60947-5-1 250 A DC conforming to IEC 60947-5-1
Permissible Short-Time Rating	100 A 140 °F (60 °C) 1 s 120 A 140 °F (60 °C) 500 ms 140 A 140 °F (60 °C) 100 ms
Protection Type	GG fuse 10 A
Mechanical Durability	30 Mcycles

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Minimum Switching Current	5 mA
Minimum Switching Voltage	17 V
Non-Overlap Time	1.5 ms on de-energisation no overlap between NC and NO contact 1.5 ms on energisation no overlap between NC and NO contact
Insulation Resistance	> 10 MOhm
Connections - Terminals	spring terminals 2 0.00 in ² (2.5 mm ²)flexible without cable end spring terminals 2 0.00 in ² (2.5 mm ²)rigid
Height	1.89 in (48 mm)
Width	1.02 in (26 mm)
Depth	1.65 in (42 mm)
Color	Dark grey

Environment

Environmental Characteristic	Normal environment
Ip Degree Of Protection	IP20 conforming to IEC 60529
Protective Treatment	TH IEC 60068
Ambient Air Temperature For Storage	-76176 °F (-6080 °C)
Ambient Air Temperature For Operation	23140 °F (-560 °C)
Operating Altitude	9842.52 ft (3000 m)

Ordering and shipping details

Category	US10I1222341
Discount Schedule	0 12
Gtin	3389110820973
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.01 in (5.1 cm)
Package 1 Width	1.65 in (4.2 cm)
Package 1 Length	1.10 in (2.8 cm)
Package 1 Weight	1.34 oz (38 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	1.18 in (3 cm)
Package 2 Width	3.39 in (8.6 cm)
Package 2 Length	10.04 in (25.5 cm)
Package 2 Weight	13.40 oz (380 g)
Unit Type Of Package 3	S02
Number Of Units In Package 3	160

Package 3 Height	5.91 in (15 cm)
Package 3 Width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	14.40 lb(US) (6.53 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations