Product data sheet

Specification





TeSys Deca, auxiliary contact block, 1 NO and 1 NC, top mount, screw clamp terminals, for LC1D09 to LC1D150 contactors

LADN11

Product availability: Stock - Normally stocked in distribution facility

Price*: 24.84 USD

Main

Range	TeSys	
3	TeSys Deca	
Product Name	TeSys Deca	
Product Or Component Type	Auxiliary contact block	
Device Short Name	LADN	
Range Compatibility	TeSys D CAD	
	TeSys D LC1D	
	TeSys F LC1F	
	TeSys F CR1F	
	TeSys Deca CAD	
	TeSys Deca LC1D	
Mounting Location	Front	
Pole Contact Composition	1 NO + 1 NC	
Contacts Operation	Instantaneous	
[Ue] Rated Operational Voltage	690 V AC 25400 Hz	
[le] Rated Operational Current	6 A at 120 V AC-15	
(,	1.04 A at 690 V AC-15	
	0.55 A at 125 V DC-13	
	0.1 A at 600 V DC-13	
	0.1 A at 000 V DO-10	
[Ui] Rated Insulation Voltage	690 V IEC 60947-5-1	
	600 V UL	
	600 V CSA	
[Ith] Conventional Free Air Thermal Current	10 A (at 140 °F (60 °C))	
Standards	EN/IEC 60947-5-1	
	UL 60947-5-1	
	CSA C22.2 No 60947-5-1	
	GB/T 14048.5	
Product Certifications	CB	
	UL	
	CSA	
	CCC	
	EAC	
	UKCA	

Complementary

Irms Rated Making Capacity
140 A AC conforming to IEC 60947-5-1
250 A DC conforming to IEC 60947-5-1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Permissible Short-Time Rating	100 A 140 °F (60 °C) 1 s 120 A 140 °F (60 °C) 500 ms 140 A 140 °F (60 °C) 100 ms
Protection Type	GG fuse 10 A
Mechanical Durability	30 Mcycles
Minimum Switching Current	5 mA
Minimum Switching Voltage	17 V
Non-Overlap Time 1.5 ms on de-energisation no overlap between NC and NO contact 1.5 ms on energisation no overlap between NC and NO contact	
Insulation Resistance	> 10 MOhm
Connections - Terminals	screw clamp terminals 1 0.000.01 in² (14 mm²)flexible with cable end screw clamp terminals 1 0.000.01 in² (14 mm²)flexible without cable end screw clamp terminals 2 0.000.00 in² (12.5 mm²)flexible with cable end screw clamp terminals 2 0.000.01 in² (14 mm²)flexible without cable end screw clamp terminals 1 0.000.01 in² (14 mm²)rigid without cable end screw clamp terminals 2 0.000.01 in² (14 mm²)rigid without cable end
Tightening Torque	15.05 lbf.in (1.7 N.m) flat Ø 6 mm 15.05 lbf.in (1.7 N.m) Philips No 2 15.05 lbf.in (1.7 N.m) pozidriv No 2
Height	1.89 in (48 mm)
Width	1.02 in (26 mm)
Depth	1.65 in (42 mm)
Color	Dark grey

Environment

Environmental Characteristic	Normal environment
Ip Degree Of Protection	IP20 conforming to IEC 60529
Protective Treatment	TH IEC 60068
Ambient Air Temperature For Storage	-76176 °F (-6080 °C)
Ambient Air Temperature For Operation	23140 °F (-560 °C)
Operating Altitude	9842.52 ft (3000 m)

Ordering and shipping details

Category	US10l1222341
Discount Schedule	0112
Gtin	3389110383836
Returnability	Yes
Country Of Origin	ID

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.18 in (3.000 cm)	
Package 1 Width	1.65 in (4.200 cm)	
Package 1 Length	2.09 in (5.300 cm)	
Package 1 Weight	1.20 oz (34.000 g)	

Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	1.18 in (3.000 cm)
Package 2 Width	3.46 in (8.800 cm)
Package 2 Length	10.08 in (25.600 cm)
Package 2 Weight	12.28 oz (348.000 g)
Unit Type Of Package 3	S03
Number Of Units In Package 3	320
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	25.32 lb(US) (11.486 kg)

Contractual warranty

Warranty 18 months

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations

Dimensions Drawings

Approximate Dimensions

