Product data sheet

Specifications



Main



Time delay auxiliary contact block, TeSys Deca, 1NO + 1NC, on delay 0.3-3s, front, spring terminals

LADT03

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 157.20 USD

mann	
Range	TeSys
0	TeSys Deca
Product Name	TeSys Deca
Product Or Component Type	Time delay auxiliary contact block
Range Compatibility	TeSys D CAD
	TeSys D LC1D
	TeSys Deca CAD
	TeSys Deca LC1D
Mounting Location	Front
Pole Contact Composition	1 NO + 1 NC
Contacts Operation	Time delay
Timer Type	On delay
Time Delay Range	0.33 s
[Ue] Rated Operational Voltage	690 V AC 25400 Hz
[Ie] Rated Operational Current	6 A at 120 V AC-15
	1.04 A at 690 V AC-15
	0.55 A at 125 V DC-13
	0.1 A at 600 V DC-13
[Ui] Rated Insulation Voltage	690 V IEC 60947-5-1
U	600 V UL
	600 V CSA
[Ith] Conventional Free Air Thermal Current	10 A (at 140 °F (60 °C))
Standards	EN/IEC 60947-5-1
	UL 60947-5-1
	CSA C22.2 No 60947-5-1
	GB/T 14048.5
	EN/IEC 60947-5-1
Product Certifications	СВ
	UL
	CSA
	CCC
	EAC
	UKCA

Complementary

Irms Rated Making Capacity	140 A AC 250 A DC
Permissible Short-Time Rating	100 A 140 °F (60 °C) 1 s 120 A 140 °F (60 °C) 500 ms 140 A 140 °F (60 °C) 100 ms

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Protection Type GG fuse 10 A Mechanical Durability 5 Mcycles Minimum Switching Current 5 mA Minimum Switching Voltage 17 V Non-Overlap Time 1.5 ms on de-energisation no overlap between NC and NO contact 1.5 ms on energisation no overlap between NC and NO contact Insulation Resistance > 10 MOhm Connections - Terminals spring terminals 2 0.00 in² (2.5 mm²)flexible without cable end spring terminals 2 0.00 in² (2.5 mm²)rigid Height 1.89 in (48 mm) Width 1.73 in (44 mm) Depth 2.40 in (61 mm) Color Dark grey		
Minimum Switching Current 5 mA Minimum Switching Voltage 17 V Non-Overlap Time 1.5 ms on de-energisation no overlap between NC and NO contact 1.5 ms on energisation no overlap between NC and NO contact Insulation Resistance > 10 MOhm Connections - Terminals spring terminals 2 0.00 in² (2.5 mm²)flexible without cable end spring terminals 2 0.00 in² (2.5 mm²)rigid Height 1.89 in (48 mm) Width 1.73 in (44 mm) Depth 2.40 in (61 mm)	Protection Type	GG fuse 10 A
Minimum Switching Voltage 17 V Non-Overlap Time 1.5 ms on de-energisation no overlap between NC and NO contact 1.5 ms on energisation no overlap between NC and NO contact Insulation Resistance > 10 MOhm Connections - Terminals spring terminals 2 0.00 in² (2.5 mm²)flexible without cable end spring terminals 2 0.00 in² (2.5 mm²)rigid Height 1.89 in (48 mm) Width 1.73 in (44 mm) Depth 2.40 in (61 mm)	Mechanical Durability	5 Mcycles
Non-Overlap Time 1.5 ms on de-energisation no overlap between NC and NO contact Insulation Resistance > 10 MOhm Connections - Terminals spring terminals 2 0.00 in² (2.5 mm²)flexible without cable end spring terminals 2 0.00 in² (2.5 mm²)rigid Height 1.89 in (48 mm) Width 1.73 in (44 mm) Depth 2.40 in (61 mm)	Minimum Switching Current	5 mA
1.5 ms on energisation no overlap between NC and NO contact Insulation Resistance > 10 MOhm Connections - Terminals spring terminals 2 0.00 in² (2.5 mm²)flexible without cable end spring terminals 2 0.00 in² (2.5 mm²)rigid Height 1.89 in (48 mm) Width 1.73 in (44 mm) Depth 2.40 in (61 mm)	Minimum Switching Voltage	17 V
Connections - Terminals spring terminals 2 0.00 in² (2.5 mm²)flexible without cable end spring terminals 2 0.00 in² (2.5 mm²)rigid Height 1.89 in (48 mm) Width 1.73 in (44 mm) Depth 2.40 in (61 mm)	Non-Overlap Time	
Height 1.89 in (48 mm) Width 1.73 in (44 mm) Depth 2.40 in (61 mm)	Insulation Resistance	> 10 MOhm
Width 1.73 in (44 mm) Depth 2.40 in (61 mm)	Connections - Terminals	
Depth 2.40 in (61 mm)	Height	1.89 in (48 mm)
	Width	1.73 in (44 mm)
Color Dark grey	Depth	2.40 in (61 mm)
	Color	Dark grey

Environment

Environmental Characteristic	Normal environment
Ip Degree Of Protection	IP2X conforming to IEC 60529
Protective Treatment	TH IEC 60068
Ambient Air Temperature For Storage	-76176 °F (-6080 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Operating Altitude	9842.52 ft (3000 m)

Ordering and shipping details

Category	US10I1222341
Discount Schedule	0112
Gtin	3389110821406
Returnability	No
Country Of Origin	FR

Packing Units

0	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.05 in (5.2 cm)
Package 1 Width	2.56 in (6.5 cm)
Package 1 Length	1.85 in (4.7 cm)
Package 1 Weight	2.82 oz (80.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	2.05 in (5.2 cm)
Package 2 Width	5.31 in (13.5 cm)
Package 2 Length	9.45 in (24.0 cm)
Package 2 Weight	28.22 oz (800.0 g)

Unit Type Of Package 3	S02
Number Of Units In Package 3	70
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	11.81 in (30.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	12.81 lb(US) (5.812 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov