

LC1DWK12B7

TeSys LC1D.K capacitor duty contactor - 3P - 60 kVAR - 415 V - 24 V AC coil

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 1,550.00 USD



Main

Range	TeSys
Product name	TeSys LC1D.K
Product or component type	Capacitor duty contactor
Device short name	LC1DWK
Contactor application	Power factor correction
Utilisation category	AC-6B
Poles description	3P
Power pole contact composition	3 NO
Device location in system	Inside delta interruption Line interruption
System Voltage	<= 690 V AC 50/60 Hz power circuit
Reactive power rating	63 kvar at 400...415 V AC 50/60 Hz <= 60 °C 35 kvar at 230 V AC 50/60 Hz <= 60 °C 67 kvar at 440 V AC 50/60 Hz <= 60 °C 104 kvar at 660...690 V AC 50/60 Hz <= 60 °C
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	24 V AC 50/60 Hz
Auxiliary contact composition	1 NO + 2 NC signalling circuit 3 NO early make power circuit
Electrical durability	300000 cycles at Ue 400 V 200000 cycles at Ue 690 V
Mounting support	DIN rail Plate
Standards	IEC 60947-4-1 CSA C22.2 No 60947-4-1 UL 60947-4-1
Product certifications	EAC CSA UL CCC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

IEC
KC

Connections - terminals	Control circuit: screw clamp terminals 2 cable(s) 0...0 in ² (1...2.5 mm ²) - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 1 cable(s) 0...0.01 in ² (1...4 mm ²) - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable(s) 0...0.01 in ² (1...4 mm ²) - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 1 cable(s) 0...0.01 in ² (1...4 mm ²) - cable stiffness: solid - without cable end Control circuit: screw clamp terminals 2 cable(s) 0...0.01 in ² (1...4 mm ²) - cable stiffness: solid - without cable end Control circuit: screw clamp terminals 1 cable(s) 0...0 in ² (1...2.5 mm ²) - cable stiffness: flexible - with cable end Power circuit : EverLink BTR screw connectors 1 cable(s) 4...50 mm ² - cable stiffness: solid - without cable end Power circuit : EverLink BTR screw connectors 2 cable(s) 4...25 mm ² - cable stiffness: solid - without cable end Power circuit : EverLink BTR screw connectors 1 cable(s) 4...50 mm ² - cable stiffness: flexible - with or without cable end Power circuit : EverLink BTR screw connectors 2 cable(s) 4...25 mm ² - cable stiffness: flexible - without cable end Power circuit : EverLink BTR screw connectors 2 cable(s) 4...16 mm ² - cable stiffness: flexible - with cable end
Tightening torque	Control circuit: 15.04 lbf.in (1.7 N.m) - on screw clamp terminals Power circuit : 9 N.m - on EverLink BTR screw connectors
Operating rate	100 cyc/h

Complementary

Auxiliary contacts type	Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1 Type mirror contact (1 NC) conforming to IEC 60947-4-1
-------------------------	--

Environment

IP degree of protection	IP2x conforming to IEC 60529 IP2x conforming to VDE 0106
Protective treatment	TH conforming to IEC 60068-2-30
Ambient air temperature for operation	23...140 °F (-5...60 °C)
Ambient air temperature for storage	-76...176 °F (-60...80 °C)
Operating altitude	9842.52 ft (3000 m) without derating
Height	7.09 in (180 mm)
Width	3.35 in (85 mm)
Depth	6.06 in (154 mm)
Product weight	3.64 lb(US) (1.65 kg)

Ordering and shipping details

Category	22359 - CTR, TESYS D, OPEN, 80-150A AC&DC
Discount Schedule	I12
GTIN	003389110060386
Nbr. of units in pkg.	1
Package weight(Lbs)	3.8500000000000001
Returnability	N
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0950 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available

Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------