Product data sheet

Specification





Contactor body, TeSys F, 4P(4NO), AC-1, <=440V 200A, without coil

LC1F1154

! To be discontinued on: Dec 31, 2025

① To be discontinued

TeSys

TeSys F

Contactor

LC1F

Product availability: Stock - Normally stocked in distribution facility

Price*: 552.00 USD

Main Range

Product Name

Device Short Name

Product Or Component Type

Device onort Hame	LOTI
Contactor Application	Resistive load
Utilisation Category	AC-1
Poles Description	4P
Power Pole Contact Composition	4 NO
[Ue] Rated Operational Voltage	<= 690 V AC 50/60 Hz <= 460 V DC
[le] Rated Operational Current	200 A 104 °F (40 °C)) <= 440 V AC-1
Complementary	
[Uc] Control Circuit Voltage	24575 V AC 40400 Hz with LX9 coil 24460 V DC with LX4 coil 100250 V AC 50/60 Hz with LXE coil 100380 V DC with LXE coil
[Uimp] Rated Impulse Withstand Voltage	8 kV
Overvoltage Category	III
[Ith] Conventional Free Air Thermal Current	200 A (at 104 °F (40 °C))
Irms Rated Making Capacity	1150 A conforming to IEC 60947-4-1
Rated Breaking Capacity	920 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	1100 A 104 °F (40 °C) - 10 s 640 A 104 °F (40 °C) - 30 s 520 A 104 °F (40 °C) - 1 min 400 A 104 °F (40 °C) - 3 min 320 A 104 °F (40 °C) - 10 min
Associated Fuse Rating	200 A gG at <= 440 V
Average Impedance	0.37 mOhm - Ith 200 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V IEC 60947-4-1 1500 V VDE 0110 group C
Power Dissipation Per Pole	15 W AC-1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Control Circuit Voltage Limits	Operational: 0.851.1 Uc AC 40400 Hz with LX9 coil Drop-out: 0.20.55 Uc AC 40400 Hz with LX9 coil Operational: 0.851.1 Uc DC with LX4 coil
	Drop-out: 0.150.2 Uc DC with LX4 coil
	Operational: 85275 V AC 50/60 Hz with LXE coil
	Drop-out: 060 V AC 50/60 Hz with LXE coil
	Operational: 85418 V DC with LXE coil Drop-out: 045 V DC with LXE coil
Heat Dissipation	5.97.2 W
	2.25.5 W
Operating Time	130 ms opening with LX9 coil
	3040 ms closing with LX4 coil 3050 ms opening with LX4 coil
	4080 ms closing with LXE coil
	654 ms opening with LXE coil
Mounting Support	Plate
Standards	EN 60947-4-1
	IEC 60947-4-1
	JIS C8201-4-1 EN 60947-1
	IEC 60947-1
Product Certifications	СВ
	UL
	RINA DNV
	LROS (Lloyds register of shipping)
	RMRoS
	CSA
	ABS
	BV
	UKCA
Connections - Terminals	Power circuit lugs-ring terminals 1 0.15 in² (95 mm²)
	Power circuit connector 1 0.15 in² (95 mm²)
	Power circuit bar 2 20 x 3 mm Power circuit bolted connection
	Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)flexible without
	cable end Control circuit screw clamp terminals 2 0.000.01 in² (14 mm²)flexible with cable
	end Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)flexible with cable
	end
	Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²)solid without cable end
	Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)
	Control circuit screw clamp terminals 2 0.000.01 in² (14 mm²)
	Control circuit screw clamp terminals 1.0 0.000.00 in² (0.22.5 mm²)flexible without cable end
	Control circuit screw clamp terminals 1.0 0.000.00 in² (0.252.5 mm²)flexible with
	cable end
	Control circuit screw clamp terminals 1.0 0.000.00 in 2 (0.22.5 mm 2) solid without cable end
Tightening Torque	Power circuit 88.51 lbf.in (10 N.m)
•	Control circuit 10.62 lbf.in (1.2 N.m) Control circuit 5.31 lbf.in (0.6 N.m)
Inmusis Devices to Va	
Inrush Power In Va	590855 VA, 40400 Hz cos phi 0.9 (at 68 °F (20 °C))with LX9 coil
	543665 VA (at 68 °F (20 °C))with LX4 coil 280310 VA, 50/60 Hz cos phi 0.5 (at 68 °F (20 °C))with LXE coil
	270320 VA (at 68 °F (20 °C))with LXE coil
Hold-In Power Consumption In Va	6.68.1 VA, 40400 Hz cos phi 0.9 (at 68 °F (20 °C))with LX9 coil
	3.944.83 VA (at 68 °F (20 °C))with LX4 coil
	4.57.0 VA, 50/60 Hz cos phi 0.5 (at 68 °F (20 °C))with LXE coil 2.54.0 VA (at 68 °F (20 °C))with LXE coil
Maximum Operating Rate	2400 cyc/h 131 °F (55 °C)
Compatibility Code	LC1F
	2011

Environment

Ip Degree Of Protection	IP2X front face with shrouds IEC 60529 IP2X front face with shrouds VDE 0106
Protective Treatment	TH
Ambient Air Temperature For Operation	-40140 °F (-4060 °C)
Ambient Air Temperature For Storage	-76176 °F (-6080 °C)
Permissible Ambient Air Temperature Around The Device	140158 °F (6070 °C) at Uc
Operating Altitude	9842.52 ft (3000 m) without derating
Mechanical Robustness	Vibrations contactor open2 Gn, 5300 Hz Vibrations contactor closed6 Gn, 5300 Hz Shocks contactor open9 Gn for 1/2 sine wave (11 ms) Shocks contactor closed15 Gn for 1/2 sine wave (11 ms)
Height	6.38 in (162 mm)
Width	7.89 in (200.5 mm)
Depth	6.73 in (171 mm)
Net Weight	8.44 lb(US) (3.83 kg)

Ordering and shipping details

Category	US10I1222336
Discount Schedule	0112
Gtin	3389110122237
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.46 in (21.500 cm)
Package 1 Width	7.87 in (20.000 cm)
Package 1 Length	10.43 in (26.500 cm)
Package 1 Weight	9.28 lb(US) (4.208 kg)
Unit Type Of Package 2	P06
Number Of Units In Package 2	18
Package 2 Height	29.53 in (75.000 cm)
Package 2 Width	23.62 in (60.000 cm)
Package 2 Length	31.50 in (80.000 cm)
Package 2 Weight	185.73 lb(US) (84.244 kg)

Contractual warranty

Warranty 18 months

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Circularity Profile	End of Life Information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Eu Rohs Directive	Compliant with Exemptions
Reach Regulation	REACh Declaration