Product data sheet

Specification





TeSys F contactor - 3P (3 NO) - AC-3 - <= 440 V 150 A - coil 380V AC

LC1F150Q7

! To be discontinued on: Dec 31, 2025

! Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	TeSys
Range Of Product	TeSys F
Product Or Component Type	Contactor
Device Short Name	LC1F
Contactor Application	Motor control Resistive load
Utilisation Category	AC-1 AC-4 AC-3
Poles Description	3P
[Ue] Rated Operational Voltage	<= 690 V AC 50/60 Hz <= 460 V DC
[Uc] Control Circuit Voltage	380 V AC 40400 Hz
[le] Rated Operational Current	250 A (at <104 °F (40 °C)) at <= 440 V AC-1 150 A (at <131 °F (55 °C)) at <= 440 V AC-3

Complementary

[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	250 A (at 104 °F (40 °C))
Rated Breaking Capacity	1200 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	1200 A 104 °F (40 °C) - 10 s 700 A 104 °F (40 °C) - 30 s 600 A 104 °F (40 °C) - 1 min 450 A 104 °F (40 °C) - 3 min 350 A 104 °F (40 °C) - 10 min
Associated Fuse Rating	160 A aM at <= 440 V 250 A gG at <= 440 V
Average Impedance	0.35 mOhm - Ith 250 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V IEC 60947-4-1 1500 V VDE 0110 group C
Power Dissipation Per Pole	22 W AC-1 8 W AC-3
Overvoltage Category	III
Power Pole Contact Composition	3 NO

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Motor Power Kw	75 kW at 380400 V AC 50/60 Hz (AC-3)
	80 kW at 415 V AC 50/60 Hz (AC-3)
	80 kW at 440 V AC 50/60 Hz (AC-3)
	90 kW at 500 V AC 50/60 Hz (AC-3)
	100 kW at 660690 V AC 50/60 Hz (AC-3)
	40 kW at 220230 V AC 50/60 Hz (AC-3)
	22 kW at 400 V AC 50/60 Hz (AC-4)
Control Circuit Voltage Limits	Operational 0.851.1 Uc 40400 Hz 131 °F (55 °C))
	Drop-out 0.20.55 Uc 40400 Hz 131 °F (55 °C))
Mechanical Durability	10 Mcycles
Inrush Power In Va	770 VA, 40400 Hz 0.9 68 °F (20 °C))
Hold-In Power Consumption In Va	8.1 VA, 40400 Hz 0.9 68 °F (20 °C))
Maximum Operating Rate	2400 cyc/h 131 °F (55 °C)
Operating Time	25 ma alasina at IIa
Operating Time	35 ms closing at Uc) 130 ms opening at Uc)
Connections - Terminals	Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)flexible without
	cable end Control circuit screw clamp terminals 2 0.000.01 in² (14 mm²)flexible without
	cable end Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)flexible with cable
	end Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²)flexible with cable
	end Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)solid without cable
	end Control circuit screw clamp terminals 2 0.000.01 in² (14 mm²)solid without cable
	end
	Power circuit bar 2 25 x 3 mm
	Power circuit lugs-ring terminals 1 0.19 in² (120 mm²)
	Power circuit connector 1 0.19 in² (120 mm²)
	Power circuit bolted connection
Tightening Torque	Control circuit 10.62 lbf.in (1.2 N.m)
	Power circuit 159.31 lbf.in (18 N.m)
Mounting Support	Plate
Heat Dissipation	5.97.2 W
Standards	IEC 60947-4-1
	JIS C8201-4-1
	EN 60947-4-1
	EN 60947-1
	IEC 60947-1
Product Certifications	DNV
	CCC
	ABS
	BV RINA
	LROS (Lloyds register of shipping)
	RMRoS
	UL
	CB
	UKCA
Compatibility Code	LC1F
Control Circuit Type	AC 40400 Hz
Environment	
Ip Degree Of Protection	IP2X front face with shrouds IEC 60529 IP2X front face with shrouds VDE 0106
Protective Treatment	тн
Ambient Air Temperature For Operation	-40140 °F (-4060 °C)
Ambient Air Temperature For	-76176 °F (-6080 °C)
Storage	

Permissible Ambient Air Temperature Around The Device	140158 °F (6070 °C) at Uc
Height	6.69 in (170 mm)
Width	6.44 in (163.5 mm)
Depth	6.73 in (171 mm)
Operating Altitude	9842.52 ft (3000 m) without derating
Net Weight	7.56 lb(US) (3.43 kg)

Ordering and shipping details

Category	US10l1222336
Discount Schedule	0112
Gtin	3389110350999
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.27 in (21.0 cm)
Package 1 Width	7.87 in (20.0 cm)
Package 1 Length	9.45 in (24.0 cm)
Package 1 Weight	9.24 lb(US) (4.19 kg)

Contractual warranty

Warranty 18 months

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Circularity Profile	End of Life Information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Eu Rohs Directive	Compliant with Exemptions
Reach Regulation	REACh Declaration