



Price* : 1,214.00 USD

LB6LD03M21 has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

Main

Range	TeSys
Device short name	LB6LD
Product or component type	Protection module
Range compatibility	TeSys Integral contactor breaker
Poles description	3P
Utilisation category	AC-43
System Voltage	690 V AC 50/60 Hz
Magnetic tripping current	108...216 A
Trip unit technology	Magnetic
Protection type	Phase imbalance
Thermal overload class	Class 20

Complementary

Motor power kW	11 kW at 480...525 V AC 50/60 Hz 15 kW at 600...690 V AC 50/60 Hz 4 kW at 220...240 V AC 50/60 Hz 9 kW at 400...415 V AC 50/60 Hz 9 kW at 440 V AC 50/60 Hz
Product weight	1.72 lb(US) (0.78 kg)

Environment

Standards	NF C 63-650
Protective treatment	TH
IP degree of protection	IP20 B conforming to IEC 60144 IP20 B conforming to IEC 60529
Ambient air temperature for operation	-4...140 °F (-20...60 °C)

Ordering and shipping details

Category	18402 - WORLD SERVICE PARTS(CONTROL ACCESS)
Discount Schedule	CP10
Nbr. of units in pkg.	1
Package weight(Lbs)	2.3999999999999999
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0841 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------