Product data sheet

Specification





TeSys F contactor - 3P (3 NO) - AC-3 - <= 440 V 275 A - coil 380 V AC

LC1F185Q6

! Discontinued on: Jan 23, 2021

! Discontinued

Main

Range	TeSys	
Range Of Product	TeSys F	
Product Or Component Type	Contactor	
Device Short Name	LC1F	
Contactor Application	Resistive load Motor control	
Utilisation Category	AC-3 AC-4 AC-1	
Poles Description	3P	
[Ue] Rated Operational Voltage	<= 460 V DC <= 690 V AC 50/60 Hz	
[Uc] Control Circuit Voltage	380 V AC 60 Hz	
[le] Rated Operational Current	275 A (at <104 °F (40 °C)) at <= 440 V AC-1 185 A (at <131 °F (55 °C)) at <= 440 V AC-3	

Complementary

[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	275 A (at 104 °F (40 °C))
Rated Breaking Capacity	1480 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	1500 A 104 °F (40 °C) - 10 s 920 A 104 °F (40 °C) - 30 s 740 A 104 °F (40 °C) - 1 min 500 A 104 °F (40 °C) - 3 min 400 A 104 °F (40 °C) - 10 min
Associated Fuse Rating	200 A aM at <= 440 V 315 A gG at <= 440 V
Average Impedance	0.33 mOhm - Ith 275 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V IEC 60947-4-1 1500 V VDE 0110 group C
Power Dissipation Per Pole	12 W AC-3 25 W AC-1
Overvoltage Category	III
Power Pole Contact Composition	3 NO

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Motor Power Kw	90 kW at 380400 V AC 50/60 Hz (AC-3) 100 kW at 415 V AC 50/60 Hz (AC-3) 100 kW at 440 V AC 50/60 Hz (AC-3) 110 kW at 500 V AC 50/60 Hz (AC-3) 110 kW at 660690 V AC 50/60 Hz (AC-3) 55 kW at 220230 V AC 50/60 Hz (AC-3) 33 kW at 400 V AC 50/60 Hz (AC-4)
Control Circuit Voltage Limits	Operational 0.851.1 Uc 50/60 Hz 131 °F (55 °C)) Drop-out 0.350.55 Uc 50/60 Hz 131 °F (55 °C))
Mechanical Durability	10 Mcycles
Inrush Power In Va	970 VA, 60 Hz 0.3 68 °F (20 °C))
Hold-In Power Consumption In Va	66 VA, 60 Hz 0.3 68 °F (20 °C))
Maximum Operating Rate	2400 cyc/h 131 °F (55 °C)
Operating Time	2035 ms closing 715 ms opening
Connections - Terminals	Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)flexible without cable end Control circuit screw clamp terminals 2 0.000.01 in² (14 mm²)flexible without cable end Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)flexible with cable end Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²)flexible with cable end Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)solid without cable end Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)solid without cable end Control circuit screw clamp terminals 2 0.000.01 in² (14 mm²)solid without cable end Power circuit bar 2 25 x 3 mm Power circuit lugs-ring terminals 1 0.23 in² (150 mm²) Power circuit connector 1 0.23 in² (150 mm²) Power circuit bolted connection
Tightening Torque	Control circuit 10.62 lbf.in (1.2 N.m) Power circuit 159.31 lbf.in (18 N.m)
Mounting Support	Plate
Heat Dissipation	1824 W
Standards	IEC 60947-4-1 EN 60947-1 IEC 60947-1 JIS C8201-4-1 EN 60947-4-1
Product Certifications	LROS (Lloyds register of shipping) CCC RMRoS UL CB RINA ABS BV DNV
Compatibility Code	LC1F
Control Circuit Type	AC 60 Hz
Environment	
Ip Degree Of Protection	IP2X front face with shrouds IEC 60529
	IP2X front face with shrouds VDE 0106
Protective Treatment	TH
Protective Treatment Ambient Air Temperature For Operation	
Ambient Air Temperature For	TH

Height	6.85 in (174 mm)
Width	6.63 in (168.5 mm)
Depth	7.13 in (181 mm)
Operating Altitude	9842.52 ft (3000 m) without derating
Net Weight	10.25 lb(US) (4.65 kg)

Ordering and shipping details

Category	22336-CTR,F-LINE,AC,OPEN,NONREV
Discount Schedule	112
Gtin	3389118093584
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.46 in (21.5 cm)
Package 1 Width	8.27 in (21 cm)
Package 1 Length	9.45 in (24 cm)
Package 1 Weight	11.25 lb(US) (5.105 kg)

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
	Rohs Exemption Information	Yes
②	Pvc Free	

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov