Product data sheet

Specifications





() Discontinued

TeSys F contactor - 3P (3 NO) -AC-3 - <= 440 V 275 A - coil 440 V AC

LC1F185R6

Discontinued on: Jul 12, 2021

Main

Range	TeSys
Range Of Product	TeSys F
Product Or Component Type	Contactor
Device Short Name	LC1F
Contactor Application	Resistive load Motor control
Utilisation Category	AC-3 AC-4 AC-1
Poles Description	3P
[Ue] Rated Operational Voltage	<= 460 V DC <= 690 V AC 50/60 Hz
[Uc] Control Circuit Voltage	440 V AC 60 Hz
[le] Rated Operational Current	275 A (at <104 °F (40 °C)) at <= 440 V AC-1 185 A (at <131 °F (55 °C)) at <= 440 V AC-3

Complementary

[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	275 A (at 104 °F (40 °C))
Rated Breaking Capacity	1480 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	1500 A 104 °F (40 °C) - 10 s 920 A 104 °F (40 °C) - 30 s 740 A 104 °F (40 °C) - 1 min 500 A 104 °F (40 °C) - 3 min 400 A 104 °F (40 °C) - 10 min
Associated Fuse Rating	200 A aM at <= 440 V 315 A gG at <= 440 V
Average Impedance	0.33 mOhm - Ith 275 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V IEC 60947-4-1 1500 V VDE 0110 group C
Power Dissipation Per Pole	12 W AC-3 25 W AC-1
Overvoltage Category	III
Power Pole Contact Composition	3 NO

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Life Is On Schneider

Motor Power Kw	90 kW at 380400 V AC 50/60 Hz (AC-3)
	100 kW at 415 V AC 50/60 Hz (AC-3)
	100 kW at 440 V AC 50/60 Hz (AC-3)
	110 kW at 500 V AC 50/60 Hz (AC-3)
	110 kW at 660690 V AC 50/60 Hz (AC-3)
	55 kW at 220230 V AC 50/60 Hz (AC-3)
	33 kW at 400 V AC 50/60 Hz (AC-4)
	55 KW at 400 V AC 50/00 Hz (AC-4)
Control Circuit Voltage Limits	Operational 0.851.1 Uc 50/60 Hz 131 °F (55 °C))
	Drop-out 0.350.55 Uc 50/60 Hz 131 °F (55 °C))
Machanical Durchility	
Mechanical Durability	10 Mcycles
Inrush Power In Va	970 VA, 60 Hz 0.3 68 °F (20 °C))
Hold-In Power Consumption In Va	66 VA, 60 Hz 0.3 68 °F (20 °C))
Maximum Operating Rate	2400 cyc/h 131 °F (55 °C)
Operating Time	2035 ms closing
	715 ms opening
Connections - Terminals	Control circuit screw clamp terminals 1 0.000.01 in ² (14 mm ²)flexible without
	Control circuit screw clamp terminals 2 0.000.01 in ² (14 mm ²)flexible without cable end
	Control circuit screw clamp terminals 1 0.000.01 in ² (14 mm ²)flexible with cable end
	Control circuit screw clamp terminals 2 0.000.00 in ² (12.5 mm ²)flexible with cable end
	Control circuit screw clamp terminals 1 0.000.01 in ² (14 mm ²)solid without cable
	end
	Control circuit screw clamp terminals 2 0.000.01 in ² (14 mm ²)solid without cable
	end
	Power circuit bar 2 25 x 3 mm
	Power circuit lugs-ring terminals 1 0.23 in ² (150 mm ²)
	Power circuit connector 1 0.23 in ² (150 mm ²) Power circuit bolted connection
Tightening Torque	Control circuit 10.62 lbf.in (1.2 N.m)
	Power circuit 159.31 lbf.in (18 N.m)
Mounting Support	
Mounting Support	Plate
Heat Dissipation	1824 W
Standards	EN 60947-1
	IEC 60947-4-1
	JIS C8201-4-1
	IEC 60947-1
	EN 60947-4-1
Product Certifications	RINA
	CB
	LROS (Lloyds register of shipping)
	DNV
	CCC
	BV
	UL
	RMRoS
	ABS
Compatibility Code	LC1F
Control Circuit Type	AC 60 Hz

Environment

Ip Degree Of Protection	IP2X front face with shrouds IEC 60529 IP2X front face with shrouds VDE 0106
Protective Treatment	тн
Ambient Air Temperature For Operation	23131 °F (-555 °C)
Ambient Air Temperature For Storage	-76176 °F (-6080 °C)
Permissible Ambient Air Temperature Around The Device	-40158 °F (-4070 °C)

Height	6.85 in (174 mm)
Width	6.63 in (168.5 mm)
Depth	7.13 in (181 mm)
Operating Altitude	9842.52 ft (3000 m) without derating
Net Weight	10.25 lb(US) (4.65 kg)

Ordering and shipping details

Category	22336-CTR,F-LINE,AC,OPEN,NONREV
Discount Schedule	112
Gtin	3389110459920
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.27 in (21 cm)
Package 1 Width	7.87 in (20 cm)
Package 1 Length	9.45 in (24 cm)
Package 1 Weight	11.29 lb(US) (5.122 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Weee Circularity Profile	