Product data sheet

Specification





Contactor, TeSys Deca, 3P(3 NO), AC-3, 0 to 440V, 12A, 36VDC coil

LC1D126CD

! Discontinued

Main

Range	TeSys TeSys Deca	
Range Of Product	TeSys Deca	
Product Or Component Type	Contactor	
Device Short Name	LC1D	
Contactor Application	Resistive load Motor control	
Utilisation Category	AC-1 AC-4 AC-3	
Poles Description	3P	_
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC	
[le] Rated Operational Current	25 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit 12 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit	
[Uc] Control Circuit Voltage	36 V DC	_

Complementary

Motor Power Kw	3 kW at 220230 V AC 50/60 Hz (AC-3)
	5.5 kW at 380400 V AC 50/60 Hz (AC-3)
	5.5 kW at 415440 V AC 50/60 Hz (AC-3)
	7.5 kW at 500 V AC 50/60 Hz (AC-3)
	7.5 kW at 660690 V AC 50/60 Hz (AC-3)
	3.7 kW at 400 V AC 50/60 Hz (AC-4)
Maximum Horse Power Rating	0.5 hp at 115 V AC 50/60 Hz for 1 phase motors
	2 hp at 230/240 V AC 50/60 Hz for 1 phase motors
	3 hp at 200/208 V AC 50/60 Hz for 3 phase motors
	3 hp at 230/240 V AC 50/60 Hz for 3 phase motors
	7.5 hp at 460/480 V AC 50/60 Hz for 3 phase motors
	10 hp at 575/600 V AC 50/60 Hz for 3 phase motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With
[Ith] Conventional Free Air	25 A (at 140 °F (60 °C)) for power circuit
Thermal Current	10 A (at 140 °F (60 °C)) for signalling circuit
Irms Rated Making Capacity	250 A at 440 V for power circuit conforming to IEC 60947
	140 A AC for signalling circuit conforming to IEC 60947-5-1
	250 A DC for signalling circuit conforming to IEC 60947-5-1
Rated Breaking Capacity	250 A at 440 V for power circuit conforming to IEC 60947

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[lcw] Rated Short-Time Withstand Current	105 A 104 °F (40 °C) - 10 s for power circuit 210 A 104 °F (40 °C) - 1 s for power circuit 30 A 104 °F (40 °C) - 10 min for power circuit 61 A 104 °F (40 °C) - 1 min for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 40 A gG at <= 690 V coordination type 1 for power circuit 25 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2.5 mOhm - Ith 25 A 50 Hz for power circuit
Power Dissipation Per Pole	0.36 W AC-3 1.56 W AC-1
[Ui] Rated Insulation Voltage	Power circuit 690 V IEC 60947-4-1 Power circuit 600 V CSA Power circuit 600 V UL Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	30 Mcycles
Electrical Durability	2 Mcycles 12 A AC-3 <= 440 V 0.8 Mcycles 25 A AC-1 <= 440 V
Control Circuit Type	DC standard
Coil Technology	With integral suppression device
Control Circuit Voltage Limits	0.10.25 Uc -40158 °F (-4070 °C) drop-out DC 0.71.25 Uc -40140 °F (-4060 °C) operational DC 11.25 Uc 140158 °F (6070 °C) operational DC
Inrush Power In W	5.4 W 68 °F (20 °C))
Hold-In Power Consumption In W	5.4 W 68 °F (20 °C)
Operating Time	63 ±15 % ms closing 20 ±20 % ms opening
Time Constant	28 ms
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)
Connections - Terminals	Control circuit: lugs-ring terminals - external diameter: 0.31 in (8 mm) Power circuit: lugs-ring terminals - external diameter: 0.31 in (8 mm)
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) lugs-ring terminals flat Ø 6 mm M3.5 Control circuit 15.05 lbf.in (1.7 N.m) lugs-ring terminals Philips No 2 M3.5 Power circuit 15.05 lbf.in (1.7 N.m) lugs-ring terminals flat Ø 8 mm M3.5 Power circuit 15.05 lbf.in (1.7 N.m) lugs-ring terminals Philips No 2 M3.5 Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2 Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals pozidriv No 2
Auxiliary Contact Composition	1 NO + 1 NC
Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Voltage	17 V for signalling circuit
Minimum Switching Current	5 mA for signalling circuit
Insulation Resistance	> 10 MOhm for signalling circuit

Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact1.5 ms on energisation between NC and NO contact
Mounting Support	Rail Plate

Environment

Standards	CSA C22.2 No 14
	EN 60947-4-1
	EN 60947-5-1
	IEC 60947-4-1
	IEC 60947-5-1
	UL 508
	IEC 60335-1
	IEG 00333-1
Product Certifications	GOST
	LROS (Lloyds register of shipping)
	CCC
	UL
	CSA
	BV
	RINA
	DNV
	GL
Ip Degree Of Protection	IP20 front face IEC 60529
Protective Treatment	THIEC 60068-2-30
Climatic Withstand	IACS E10 exposure to damp heat
	IEC 60947-1 Annex Q category D exposure to damp heat
Permissible Ambient Air	-40140 °F (-4060 °C)
Temperature Around The Device	140158 °F (6070 °C) with derating
Operating Altitude	09842.52 ft (03000 m)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open 2 Gn, 5300 Hz)
	Vibrations contactor closed 4 Gn, 5300 Hz)
	Shocks contactor open 10 Gn for 11 ms)
	Shocks contactor closed 15 Gn for 11 ms)
	Shocks contactor closed to Office 11 ms)
Height	3.03 in (77 mm)
Width	1.77 in (45 mm)
Depth	3.74 in (95 mm)
Net Weight	1.07 lb(US) (0.485 kg)
	ו.טו וטוניטן (טידיט תשן

Ordering and shipping details

Category	22355-CTR,TESYS D,OPEN,9-38A DC
Discount Schedule	112
Gtin	00785901865186
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information