Product data sheet

Specification





IEC contactor, TeSys Deca, nonreversing, 125A resistive, 4 pole, 2 NO and 2 NC, 220VAC 50/60Hz coil, open style

LC1D80008M7

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 518.00 USD

Main

Range	TeSys
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load
Utilisation Category	AC-1
Poles Description	4P
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz
[le] Rated Operational Current	125 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit
[Uc] Control Circuit Voltage	220 V AC 50/60 Hz

Complementary

Compatibility Code	LC1D
Pole Contact Composition	2 NO + 2 NC
Protective Cover	Without
[Ith] Conventional Free Air Thermal Current	125 A (at 140 °F (60 °C)) for power circuit
Irms Rated Making Capacity	1100 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	1100 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	640 A 104 °F (40 °C) - 10 s for power circuit 990 A 104 °F (40 °C) - 1 s for power circuit 135 A 104 °F (40 °C) - 10 min for power circuit 320 A 104 °F (40 °C) - 1 min for power circuit
Associated Fuse Rating	200 A gG at <= 690 V coordination type 1 for power circuit 160 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	0.8 mOhm - Ith 125 A 50 Hz for power circuit
Power Dissipation Per Pole	12.5 W AC-1
[Ui] Rated Insulation Voltage	Power circuit 600 V CSA Power circuit 600 V UL Power circuit 1000 V IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	4 Mcycles
Electrical Durability	0.8 Mcycles 125 A AC-1 <= 440 V
Control Circuit Type	AC 50/60 Hz
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.851.1 Uc -40131 °F (-4055 °C) operational AC 60 Hz 0.30.6 Uc -40131 °F (-4055 °C) drop-out AC 50/60 Hz 0.81.1 Uc -40131 °F (-4055 °C) operational AC 50 Hz
Inrush Power In Va	245 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C)) 245 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	26 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C)) 26 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat Dissipation	610 W at 50/60 Hz
Operating Time	2035 ms closing 620 ms opening
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)
Connections - Terminals	Control circuit: screw clamp terminals 2 0.000.00 in² (12.5 mm²) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 0.000.00 in² (12.5 mm²) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end Power circuit: connector 1 0.010.08 in² (450 mm²) - cable stiffness: flexible without cable end Power circuit: connector 2 0.010.04 in² (450 mm²) - cable stiffness: flexible with cable end Power circuit: connector 2 0.010.02 in² (416 mm²) - cable stiffness: flexible with cable end Power circuit: connector 2 0.010.08 in² (450 mm²) - cable stiffness: solid without cable end Power circuit: connector 2 0.010.08 in² (450 mm²) - cable stiffness: solid without cable end
Tightening Torque	Control circuit 10.62 lbf.in (1.2 N.m) screw clamp terminals flat Ø 6 mm Control circuit 10.62 lbf.in (1.2 N.m) screw clamp terminals Philips No 2 Power circuit 106.21 lbf.in (12 N.m) connector flat Ø 6 to Ø 8 mm Power circuit 106.21 lbf.in (12 N.m) connector hexagonal 0.16 in (4 mm) Control circuit 10.62 lbf.in (1.2 N.m) screw clamp terminals pozidriv No 2
Mounting Support	Plate Rail

Environment

Standards	EN 60947-4-1	
	EN 60947-5-1	
	IEC 60947-4-1	
	IEC 60947-5-1	
	UL 60947-4-1	
	UL 60947-5-1	
	CSA C22.2 No 60947-4-1	
	CSA C22.2 No 60947-5-1	
	GB/T 14048.4	

Product Certifications	UL
	CSA
	CCC
	EAC
	UKCA
	CB
	EU-RO-MR by DNV-GL
Ip Degree Of Protection	IP20 front face IEC 60529
Protective Treatment	THIEC 60068-2-30
Climatic Withstand	IACS E10 exposure to damp heat
Permissible Ambient Air	-40140 °F (-4060 °C)
Temperature Around The Device	140158 °F (6070 °C) with derating
Operating Altitude	09842.52 ft (03000 m)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open 2 Gn, 5300 Hz)
	Shocks contactor open 8 Gn for 11 ms)
	Vibrations contactor closed 3 Gn, 5300 Hz)
	Shocks contactor closed 10 Gn for 11 ms)
Height	5.00 in (127 mm)
Width	3.78 in (96 mm)
Depth	5.51 in (140 mm)
Net Weight	4.06 lb(US) (1.84 kg)

Ordering and shipping details

Category	US10I1222359
Discount Schedule	0112
Gtin	3389110075267
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.10 in (15.500 cm)
Package 1 Width	5.31 in (13.500 cm)
Package 1 Length	4.33 in (11.000 cm)
Package 1 Weight	3.89 lb(US) (1.764 kg)
Unit Type Of Package 2	S02
Number Of Units In Package 2	5
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	20.28 lb(US) (9.199 kg)

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov