

# Product data sheet

## Characteristics

# LC1F1154M6

TeSys F contactor - 4P (4 NO) - AC-1 -  $\leq 440$  V  
200 A - coil 220 V AC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 630.00 USD



### Main

Range	TeSys
Product name	TeSys F
Product or component type	Contactor
Device short name	LC1F
Contactor application	Resistive load
Utilisation category	AC-1
Poles description	4P
Power pole contact composition	4 NO
System Voltage	$\leq 690$ V AC 50/60 Hz
[Ie] rated operational current	200 A ( $\leq 104$ °F (40 °C)) at $\leq 440$ V AC-1
[Uc] control circuit voltage	220 V AC 60 Hz

### Complementary

[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	200 A at $\leq 104$ °F (40 °C)
Rated breaking capacity	920 A conforming to IEC 60947-4-1
[Icw] rated short-time withstand current	1100 A $\leq 104$ °F (40 °C) 10 s 640 A $\leq 104$ °F (40 °C) 30 s 520 A $\leq 104$ °F (40 °C) 1 min 400 A $\leq 104$ °F (40 °C) 3 min 320 A $\leq 104$ °F (40 °C) 10 min
Associated fuse rating	125 A aM at $\leq 440$ V 200 A gG at $\leq 440$ V
Average impedance	0.37 mOhm at 50 Hz - Ith 200 A
[Ui] rated insulation voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C

Power dissipation per pole	15 W AC-1
Mounting support	Plate
Standards	IEC 60947-4-1 EN 60947-4-1 IEC 60947-1 EN 60947-1 JIS C8201-4-1
Product certifications	RMRoS CCC UL RINA ABS BV CB LROS (Lloyds register of shipping) DNV
Connections - terminals	Control circuit: screw clamp terminals 2 cable(s) 0...0 in <sup>2</sup> (1...2.5 mm <sup>2</sup> ) - cable stiffness: flexible - with cable end Power circuit: connector 1 cable(s) 0.15 in <sup>2</sup> (95 mm <sup>2</sup> ) Control circuit: screw clamp terminals 1 cable(s) 0...0.01 in <sup>2</sup> (1...4 mm <sup>2</sup> ) - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable(s) 0...0.01 in <sup>2</sup> (1...4 mm <sup>2</sup> ) - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 1 cable(s) 0...0.01 in <sup>2</sup> (1...4 mm <sup>2</sup> ) - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 1 cable(s) 0...0.01 in <sup>2</sup> (1...4 mm <sup>2</sup> ) - cable stiffness: solid - without cable end Control circuit: screw clamp terminals 2 cable(s) 0...0.01 in <sup>2</sup> (1...4 mm <sup>2</sup> ) - cable stiffness: solid - without cable end Power circuit: lugs-ring terminals 1 cable(s) 0.15 in <sup>2</sup> (95 mm <sup>2</sup> ) Power circuit: bar 2 x (20 x 3 mm)
Tightening torque	Control circuit: 10.62 lbf.in (1.2 N.m) Power circuit: 88.5 lbf.in (10 N.m)
Control circuit voltage limits	0.35...0.55 U <sub>c</sub> at 131 °F (55 °C) drop-out 50/60 Hz 0.85...1.1 U <sub>c</sub> at 131 °F (55 °C) operational 50/60 Hz
Inrush power in VA	660 VA at 68 °F (20 °C) (cos φ 0.3) 60 Hz
Hold-in power consumption in VA	55 VA at 68 °F (20 °C) (cos φ 0.3) 60 Hz
Heat dissipation	12...16 W
Operating time	23...35 ms closing 5...15 ms opening
Mechanical durability	10 Mcycles
Operating rate	2400 cyc/h at ≤ 131 °F (55 °C)

## Environment

IP degree of protection	IP2x front face with shrouds (ordered separately) conforming to IEC 60529 IP2x front face with shrouds (ordered separately) conforming to VDE 0106
Protective treatment	TH
Ambient air temperature for operation	23...131 °F (-5...55 °C)
Ambient air temperature for storage	-76...176 °F (-60...80 °C)
Permissible ambient air temperature around the device	-40...158 °F (-40...70 °C)
Operating altitude	9842.52 ft (3000 m) without derating
Height	6.38 in (162 mm)
Width	7.89 in (200.5 mm)
Depth	6.73 in (171 mm)
Product weight	8.44 lb(US) (3.83 kg)

## Ordering and shipping details

Category	22336 - CTR,F-LINE,AC,OPEN,NONREV
Discount Schedule	I12
GTIN	003389118093416

Nbr. of units in pkg.	1
Package weight(Lbs)	10.620000000000001
Returnability	N
Country of origin	CZ

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------